



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. VOLTAGE" 12V DC
4. OPERATING TEMP.: -20°C TO +60°C

GREEN LED

PARAMETERS	SYMBOL	TYP.	UNITS
AVE CURRENT	I_A	19	mA
EMISION WAVELENGTH	λ_p	525	nm
LUMINOUS INTESTITY	I_F	700	mcd



TITLE 50-004-19M

B	20381	UPDATE AND CONVERT	01/05/12	BMA
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
4:1	1/5/2012	BMA	F050419	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[5000419LAMP](#)