
1.3mm DC Power Plug

171-3210-E



Dimensions: In.



7	Cap
6	Terminal B
5	Terminal A
4	Insulator B
3	Insulator A
2	Contact spring
1	Contact pin
Let	Part name

SPECIFICATIONS	
Withstand voltage:	500VAC for 1 minute
Insulation resistance:	100MΩ (min) @ 500VDC
Contact resistance:	50mΩ (max.)
Insulator material:	Polycarbonate
Temperature rating:	135°C
RoHS Compliant	

Date Last Revised: 12-8-05

Available from Mouser Electronics 1-800-346-6873 www.mouser.com

KC-300901

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn: <u>171-3210-E</u>