

GBJL15005 THRU GBJL1510

Features

- Lead Free Finish/RoHS Compliant (NOTE 1) ("P" Suffix designates RoHS Compliant. See ordering information)
- Ideal for printed circuit board
- Low forward voltage drop, high current capability.
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Halogen free available upon request by adding suffix "-HF"

Maximum Ratings

- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +150°C
- UL Recognized File # E165989
- Mounting torque: 5in-lbs.

MCC Catalog Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
GBJL15005	GBJL15005	50V	35V	50V
GBJL1501	GBJL1501	100V	70V	100V
GBJL1502	GBJL1502	200V	140V	200V
GBJL1504	GBJL1504	400V	280V	400V
GBJL1506	GBJL1506	600V	420V	600V
GBJL1508	GBJL1508	800V	560V	800V
GBJL1510	GBJL1510	1000V	700V	1000V


Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Forward Current	$I_{F(AV)}$	15 A	$T_C = 100^\circ\text{C}$
Peak Forward Surge Current	I_{FSM}	240A	8.3ms, half sine
Maximum Instantaneous Forward Voltage	V_F	1.05V	$I_{FM} = 7.5A$ $T_J = 25^\circ\text{C}$
Maximum DC Reverse Current At Rated DC Blocking Voltage	I_R	10 μA 500uA	$T_J = 25^\circ\text{C}$ $T_J = 125^\circ\text{C}$
I^2t Rating for fusing	I^2t	240A ² S	(t<8.3ms)
Typical Junction Capacitance	C_J	60 pF	Measured at 1.0MHz, $V_R=4.0V$

Notes: 1. High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7
3. Device mounted on 300mm * 300mm *1.6mm Cu Plate Heatsink


15 Amp Glass Passivated Bridge Rectifier 50 to 1000 Volts

GBJL



DIMENSIONS






DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	1.067	1.091	27.10	27.70	
B	.551	.575	14.00	14.60	
C	.570	.610	14.50	15.50	
D	.071 typ		1.80 typ		
E	.339	.354	8.60	9.00	
F	.071	.087	1.80	2.20	
G	.120	.134	3.00	3.40	
H	.110	.126	2.80	3.20	
J	.098	.114	2.50	2.90	
K	.012	.028	0.30	0.70	
L	.098	.114	2.50	2.90	
M	.035	.043	0.90	1.10	
N	.390	.400	9.80	10.20	
O	.290	.300	7.30	7.70	
P	.079	.094	2.00	2.40	
R	.150	.157	3.60	4.00	



Case Type

RATING AND CHARACTERISTIC CURVES

GBJL15005 thru GBJL1510



Ordering Information :

Device	Packing
Part Number-BP	Bulk: 2.2K/Ctn

Note : Adding "-HF" suffix for halogen free, eg. Part Number-BP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[GBJL1510-BP](#)