




PART NUMBER	MATERIAL	MARKER SIZE inches [mm]	LABELS PER ROW	STANDARD PKG. QTY.
C150X075YMT	GMY4-S	1.500" [38.10] X 0.750" [19.05]	1	5000
C150X075PBT	GMP4-W			
C150X075CBT	GMC4			
C150X075YJT	GMY4-W			

NOTES:
1. SEE MFG. DRAWING NO. A61230.
2. MILLIMETER ARE IN [].

										CAD FILENAME/LAYERS		100472HK_C10267_C150X075YJT_00.PRT			
										PANDUIT					
										CORP. TINLEY PARK, ILLINOIS					
										CUSTOMER DRAWING					
										OPTIMUM C150X075**T					
										THERMAL TRANSFER LABELS					
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .005 (.XX) ± .015 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
										DRAWN BY	MAT'L:		SCALE		
										RVU	SEE TABLE		NTS		
O	9-30-04	RVU		DRAWING RELEASE.		4992	R			DATE			DRAWING NO.		DWG
REV	DATE	BY	CHK	DESCRIPTION		ECN	- R	CUST	SUP	CHK'D			C10267		A
													SIZE		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

C150X075PBT