

D10S1H

DISCONNECT SW 600VAC 30A D10 DOOR MOUNTE

Product availability: Stock - Normally stocked in distribution facility

Main

Commercial Status	Commercialised
Range of product	D10S
Product or component type	Disconnect Switch
[In] rated current	30 A
Rated power in hp	25 hp 600 V AC 20 hp 480 V AC 10 hp 200/240 V AC 5 hp 120 V AC
[Ue] rated operational voltage	600 V AC
Mounting support	Door
NEMA size	0 1
Condition of use	Service entrance rated

Ordering and shipping details

Category	22642 - DISCONNECT SWITCHES - D10
Discount Schedule	T
GTIN	00785901118572
Nbr. of units in pkg.	1
Package weight(Lbs)	5.00
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[D10S1H](#)