XZCC12MDP40B

male, M12, 4-pin, straight connector - cable gland Pg 7

Product availability: Non-Stock - Not normally stocked in distribution facility



Main	
Commercial Status	Commercialised
Accessory / separate part category	Cabling accessories
Accessory / separate part type	Connector
Electrical connection	Straight male connector M12, 4 pins
Collar material	Plastic
Status LED	Without
Cable connection	Screw terminal / wire size <= 0 in² (0.75 mm²) / clamping capacity 0.120.24 in (36 mm)

	۱mr	NIΔI	nor	ntorv
\sim	/I I I L	лсі	1161	ntary

Cable gland type	Pg 7	
Cable connector fixing	Screw-on	
[Ue] rated operational voltage	150 V DC 125 V AC	
[In] rated current	3 A	
Enclosure material	Plastic	
Insulating resistance	> 1000 GΩ	
Contact resistance	<= 8000 μOhm	
Product weight	0.06 lb(US) (0.025 kg)	

Environment

IP degree of protection	IP67
Ambient air temperature for operation	-40185 °F (-4085 °C)

Ordering and shipping details

Category	22483 - MACHINE CABLES	
Discount Schedule	DS3	
GTIN	003389110806212	
Nbr. of units in pkg.	1	
Package weight(Lbs)	0.04	
Product availability	Non-Stock - Not normally stocked in distribution facility	
Returnability	N	
Country of origin	DE	-

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0545 - Schneider Electric declaration of conformity

Contractual warranty

P	eriod	18 months	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric: XZCC12MDP40B