



Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Commercial Status	Commercialised
Range of product	Harmony 9001SK
Product or component type	Complete pilot light
Device short name	9001SK
Lens type	Domed plastic
Light block supply	Direct 24...28 V AC/DC

### Complementary

Bezel material	Plastic
Mounting diameter	1.18 in (30 mm)
Shape of signaling unit head	Round
Cap/Operator or lens colour	White
Light source	Incandescent
Bulb base	BA 9s
Tightening torque	7.08 lbf.in (0.8 N.m) conforming to EN/IEC 60947-1
Shape of screw head	Cross slotted head
Connections - terminals	Screw clamp terminals (1 x 0.22...2 x 1.5 mm <sup>2</sup> ) conforming to EN/IEC 60947-1
[I <sub>th</sub> ] conventional free air thermal current	10 A
Short circuit protection	10 A cartridge fuse conforming to EN/IEC 60947-5-1
[U <sub>i</sub> ] rated insulation voltage	250 V (degree of pollution: 2) conforming to EN/IEC 60947-1
[U <sub>imp</sub> ] rated impulse withstand voltage	2.5 kV conforming to EN/IEC 60947-1
Operating position	Any position
CAD overall width	2.13 in (54 mm)
CAD overall height	2.76 in (70 mm)
CAD overall depth	1.65 in (42 mm)
Product weight	0.4 lb(US) (0.181 kg)

### Environment

Class of protection against electric shock	Class II
Protective treatment	TC
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 4X NEMA 4 NEMA 3R NEMA 3 NEMA 2 NEMA 13 NEMA 12 NEMA 1
Vibration resistance	7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
Ambient air temperature for operation	-13...158 °F (-25...70 °C)

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508 CSA C22.2 No 14
Product certifications	NEMA UL 508

### Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901452911
Nbr. of units in pkg.	1
Package weight(Lbs)	0.50
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0921 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001SKP35W9](#)