

### Main

Range of product	Harmony
Product or component type	Head for pilot light
Product specific application	For incandescent bulb
Cap/Operator or lens colour	Green

### Complementary

Mechanical durability	1000000 cycles
Product weight	0.015 kg

### Environment

Standards	EN/IEC 60947-5-1 CSA C22.2 No 14
Protective treatment	TH
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn (10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Class of protection against electric shock	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZA2BV03](#)