
REV	DATE	ECO#
Α	03/31/95	1342

DRAWING NOT TO SCALE ALL DIMENSIONS IN INCHES



RESISTANCE AT 25 DEG C = 2.5 DHMS +/- 15% MAX CONTINUOUS CURRENT (Imax) = 15 AMPS RESISTANCE AT Imax = 0.03 DHMS NOMINAL MAX VOLTAGE RATING = 265 VAC (RMS) MAX SURGE RATING = 87 JOULES ENCAPSULATION = SILICONE RESIN

MARKING = OPTIONAL LEADS = RODAN P/N STL-209-18

SPECIFICATIONS:

DRAWN BY D. NGUYEN	<u>AMETHERM</u>
DATE 09/25/90 DRIG. F. TISED	Circuit Protection Thermistors
REV A APP	SURGE-GARD INRUSH CURRENT LIMITER
SHEET 1 OF 1	SG160

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ametherm: