


**CUI INC****Part No: CLS0402MA-1****Description: speaker****Date: 7/03/2007****Unit: mm****Page No: 1 of 2****Specifications**




Nominal Size	40 mm	1 ½ inch.	
Impedance	8 Ohm $\pm$ 15%	at	1 KHz 1 V
Resonant frequency	530 Hz $\pm$ 150 Hz	at	1 V
Sound pressure level	90 dB/w $\pm$ 3 dB	0.5 w 50 cm ave at	0.8K, 1K, 1.2K, 1.5K Hz
Response	Fo Hz ~ 6 KHz max 10 dB		
Input power	Nominal	0.5 W	Handling capacity 1.0 W
Operation	must be normal at program source 0.5 W		
Buzz, rattle, etc.	must be normal at sine wave 2.0 V		
Magnet	Size: 12.5 x 1.5 mm		
Load test	White noise	0.5 W	for 24 hours
Heat test	65 $\pm$ 2° C	20-50% R.H.	24 hours
Humidity test	40 $\pm$ 2° C	90-95% R.H.	24 hours

Frequency Response Curve

Potentiometer range	50 dB
Rectifier	RMS
Lower limit frequency	20 Hz
Wr. speed	100 mm/sec

Zero level 70 dB

REV.	DESCRIPTION	DATE
A	NEW DRAWING	7/3/2007



SCALE 1:1

TOLERANCE:
±0.5mm UNLESS OTHERWISE
SPECIFIED

**CUI INC**

20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

TITLE: LOW PROFILE SPEAKER		REV: A
PART NO. CLS0402MA-1	UNITS: MM [INCHES]	
DRAWN BY: ZRJ	APPROVED BY:	SCALE: 2:1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Inc.:](#)

[CLS0402MA-1](#)