




SPECIFICATIONS


- 1. CASE:
24 GA. (.024) CRS, TIN PLATED
- 2. RATED CURRENT:
5A
- 3. RATED VOLTAGE:
50VDC
- 4. TEST VOLTAGE:
100VDC



INSERTION LOSS (50Ω TYPICAL)

	.05 MHz	.15 MHz	.50 MHz	1.5 MHz	5.0 MHz	20 MHz
L/L	40 db	60 db	60 db	60 db	60 db	60 db
L/G	20 db	40 db	60 db	60 db	60 db	50 db

SCHEMATIC



NEXT ASSY	USED ON
APPLICATION	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ±.030 ± .XXX ±.010	CONTRACT NO.		FILTER CONCEPTS INC.			
	APPROVALS	DATE				
MATERIAL	DRAWN GIANG TRINH	07-08-02	APPLICATION DRAWING DP5 FILTER			
	CHECKED DANNIEL VUONG	08-06-02				
FINISH			SIZE B	CODE IDENT NO.	DRAWING NO. 7394	
	SCALE	1/1			SHEET	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Astrodyne TDI:](#)

[DP5](#)