

# TEXAS INSTRUMENTS 运算放大器

RoHS Compliant 该产品符合欧盟 RoHS 标准。

TEXAS INSTRUMENTS  
Authorized Distributor

## 高速放大器 (≤ 50MHZ)

订购 500 只及以上者, 请来电询价。

贸泽电子料号	TI 料号	封装	通道个数	Vs (最小值/最大值)	每个通道的 Iq (最大值)(mA)	GBW (典型值)(MHz)	Io (典型值)(mA)	压摆率 (典型值)(V/us)	单价					
									1	25	100	250		
<b>电压反馈</b>														
595-OPA355NA/250	OPA355NA/250	SOT-6	1	2.5/5.5	14	200	100	360	20.86	16.09	14.60	11.92		
595-OPA380AID	OPA380AID	SOIC-8	1	2.7/5.5	8.8	90	-	80	52.52	42.84	38.52	35.02		
595-OPA380AIDGKT	OPA380AIDGKT	VSSOP-8	1	2.7/5.5	8.8	90	-	80	46.94	37.70	34.34	30.99		
595-THS4281D	THS4281D	SOIC-8	1	2.7/15	1	-	30	35	22.72	18.25	16.61	14.97		
595-THS4281DBVT	THS4281DBVT	SOT-5	1	2.7/15	1	-	30	35	23.47	19.15	17.21	15.65		
595-THS4281DGK	THS4281DGK	VSSOP-8	1	2.7/15	1	-	30	35	22.72	18.25	16.61	14.97		
595-OPA830IDBVT	OPA830IDBVT	SOT-5	1	2.8/11	-	-	80	-	14.90	11.40	10.36	9.31		
595-THS4304D	THS4304D	SOIC-8	1	3/5	-	-	100	830	49.39	40.45	36.51	33.53		
595-THS4304DBVT	THS4304DBVT	SOT-5	1	3/5	-	-	100	830	47.53	38.89	35.09	32.26		
595-THS4304DGK	THS4304DGK	VSSOP-8	1	3/5	-	-	100	830	49.39	40.45	36.51	33.53		
595-SN1050IDBVT	SN1050IDBVT	SOT-5	1	3/15	22	120	100	900	21.16	16.24	14.75	12.07		
595-OPA890IDBVT	OPA890IDBVT	SOT-6	1	3/12	1.2	130	40	500	22.13	17.06	15.50	13.93		
595-OPA690ID	OPA690ID	SOIC-8	1	4.5/12	6.2	300	190	1800	31.36	25.18	22.95	20.64		
595-OPA690IDBVT	OPA690IDBVT	SOT-6	1	4.5/12	6.2	300	190	1800	32.85	26.82	24.06	20.26		
595-OPA698ID	OPA698ID	SOIC-8	1	5/12	16.6	250	120	1100	47.98	38.52	35.09	31.66		
595-OPA699ID	OPA699ID	SOIC-8	1	5/12	16.6	1000	120	1400	52.52	42.84	38.52	35.02		
595-OPA820ID	OPA820ID	SOIC-8	1	5/12	6.4	280	110	240	24.59	20.04	18.03	15.12		
595-OPA820IDBVR	OPA820IDBVR	SOT-5	1	5/12	6.4	280	110	240	23.47	18.10	16.39	13.41		
595-OPA820IDBVT	OPA820IDBVT	SOT-5	1	5/12	6.4	280	110	240	23.47	19.15	17.21	15.65		
595-THS4211D	THS4211D	SOIC-8	1	5/15	24	350	200	970	53.12	43.51	39.26	36.06		
595-THS4221D	THS4221D	SOIC-8	1	5/15	-	120	100	975	25.70	20.93	18.85	15.79		
595-THS4221DBVT	THS4221DBVT	SOT-5	1	5/15	-	120	100	975	24.59	20.04	18.03	15.12		
595-THS4271D	THS4271D	SOIC-8	1	5/15	28	400	160	1000	50.29	41.20	37.18	34.20		
595-THS4271DGK	THS4271DGK	VSSOP-8	1	5/15	28	400	160	1000	50.29	41.20	37.18	34.20		
595-THS4271DGN	THS4271DGN	HTSSOP-8	1	5/15	28	400	160	1000	57.29	47.53	43.21	36.73		
595-THS4001CD	THS4001CD	SOIC-8	1	5/30	9.5	270	100	400	59.23	49.17	44.70	40.23		
595-THS4011ID	THS4011ID	SOIC-8	1	10/30	11	290	110	310	47.98	38.52	35.09	31.66		
595-THS4021CD	THS4021CD	SOIC-8	1	10/30	11	1600	100	470	72.64	59.53	53.71	49.39		
595-THS4021CDGN	THS4021CDGN	HTSSOP-8	1	10/30	11	1600	100	470	72.64	59.53	53.71	49.39		
595-THS4021ID	THS4021ID	SOIC-8	1	10/30	11	1600	100	470	74.50	61.09	55.13	50.66		
595-THS4031CD	THS4031CD	SOIC-8	1	10/30	11	100	90	100	44.70	36.51	32.78	29.80		
595-THS4031ID	THS4031ID	SOIC-8	1	10/30	11	100	90	100	43.81	35.16	32.04	28.91		
595-THS4031IDGN	THS4031IDGN	HTSSOP-8	1	10/30	11	100	90	100	47.98	38.52	35.09	31.66		
595-THS4061CD	THS4061CD	SOIC-8	1	10/30	11	100	115	400	36.88	30.10	27.04	24.59		
595-THS4061ID	THS4061ID	SOIC-8	1	10/30	11	100	115	400	36.51	29.28	26.67	24.06		
595-THS4081ID	THS4081ID	SOIC-8	1	10/30	5	100	85	230	34.64	28.24	25.40	21.31		
595-THS4601ID	THS4601ID	SOIC-8	1	10/30	11.7	180	50	100	200.48	182.15	168.74	155.33		
595-THS4631D	THS4631D	SOIC-8	1	10/30	11.5	210	95	1000	84.93	70.48	64.07	57.66		
595-THS4631DGN	THS4631DGN	HTSSOP-8	1	10/30	11.5	210	95	1000	83.81	68.69	61.98	56.99		
595-OPA656N/250	OPA656N/250	SOT-5	1	10/12	-	230	70	290	75.47	61.84	55.80	51.26		
595-OPA656NB/250	OPA656NB/250	SOT-5	1	10/12	-	230	70	290	88.51	74.43	68.39	62.36		
595-OPA656U	OPA656U	SOIC-8	1	10/12	-	230	70	290	75.47	61.84	55.80	51.26		
595-OPA656UB	OPA656UB	SOIC-8	1	10/12	-	230	70	290	88.51	74.43	68.39	62.36		
595-OPA657NB/250	OPA657NB/250	SOT-5	1	10/12	16.3	1600	70	700	94.76	79.64	73.23	66.75		
595-OPA657U	OPA657U	SOIC-8	1	10/12	16.3	1600	70	700	89.85	74.57	67.80	57.59		
595-OPA842ID	OPA842ID	SOIC-8	1	10/12	22.5	200	100	400	40.23	32.85	29.50	26.82		
595-OPA842IDBVT	OPA842IDBVT	SOT-5	1	10/12	22.5	200	100	400	36.51	29.28	26.67	24.06		
595-OPA843ID	OPA843ID	SOIC-8	1	10/12	22.5	800	100	1000	41.35	33.75	30.32	25.48		
595-OPA843IDBVT	OPA843IDBVT	SOT-5	1	10/12	22.5	800	100	1000	40.23	32.85	29.50	26.82		
595-OPA846ID	OPA846ID	SOIC-8	1	10/12	13.2	1750	80	625	44.70	36.51	32.78	29.80		
595-OPA847ID	OPA847ID	SOIC-8	1	10/12	18.9	3900	75	950	53.64	43.81	39.34	35.76		
595-OPA847IDBVT	OPA847IDBVT	SOT-6	1	10/12	18.9	3900	75	950	47.98	38.52	35.09	31.66		
595-OPA2889ID	OPA2889ID	SOIC-8	2	2.6/12	0.46	75	40	70	28.76	23.10	21.01	19.00		
595-OPA2889IDGST	OPA2889IDGST	VSSOP-10	2	2.6/12	0.46	75	40	70	29.35	23.91	20.26	19.52		
595-OPA2380AIDGKT	OPA2380AIDGKT	VSSOP-8	2	2.7/5.5	8.8	90	-	80	57.29	47.53	43.21	36.73		
595-SN10502DGK	SN10502DGK	VSSOP-8	2	3/15	22	120	100	900	30.25	24.29	22.13	19.97		
595-OPA2890ID	OPA2890ID	SOIC-8	2	3/12	1.2	-	40	400	28.76	23.10	21.01	19.00		
595-OPA2890IDGST	OPA2890IDGST	VSSOP-10	2	3/12	1.2	-	40	400	29.35	23.91	20.26	19.52		
595-OPA2830ID	OPA2830ID	SOIC-8	2	3/11	3.9	100	75	500	23.47	18.10	16.39	13.41		
595-OPA2830IDGKT	OPA2830IDGKT	VSSOP-8	2	3/11	3.9	100	75	500	23.47	18.10	16.39	13.41		
595-THS4222D	THS4222D	SOIC-8	2	5/15	-	120	100	975	30.25	24.29	22.13	19.97		
595-OPA2690I-14D	OPA2690I-14D	SOIC-14	2	5/12	6.3	300	190	1800	51.55	41.35	37.70	33.97		
595-OPA2690ID	OPA2690ID	SOIC-8	2	5/12	6.3	300	190	1800	51.55	41.35	37.70	33.97		
595-OPA2652U	OPA2652U	SOIC-8	2	6/12	7.75	200	140	335	29.35	23.91	20.26	19.52		
595-OPA2822U	OPA2822U	SOIC-8	2	6/12	6.3	240	150	170	34.64	28.31	23.91	21.38		
595-OPA2846ID	OPA2846ID	SOIC-8	2	6/12	13.35	1650	80	600	75.02	62.28	56.62	50.96		
595-THS6012CDWP	THS6012CDWP	HSOP-20	2	9/32	-	-	500	1300	81.50	63.40	53.49	49.24		
595-THS4012CDGN	THS4012CDGN	HTSSOP-8	2	10/30	11	290	110	310	69.88	57.22	51.63	47.46		
595-THS4022CD	THS4022CD	SOIC-8	2	10/30	11	1600	100	470	93.42	79.12	73.08	66.98		
595-THS4032CD	THS4032CD	SOIC-8	2	10/30	10	100	90	100	72.64	59.53	53.71	49.39		
595-THS4032CDGN	THS4032CDGN	HTSSOP-8	2	10/30	11	100	90	100	76.36	62.58	56.47	51.93		
595-THS4032ID	THS4032ID	SOIC-8	2	10/30	11	100	90	100	74.50	61.09	55.13	50.66		
595-THS4042CD	THS4042CD	SOIC-8	2	10/30	11	60	100	400	94.62	74.05	71.37	60.72		
595-THS4052CD	THS4052CD	SOIC-8	2	10/30	11.5	38	100	240	34.64	27.79	25.33	22.87		
595-THS4052ID	THS4052ID	SOIC-8	2	10/30	11.5	38	100	240	36.73	29.50	26.82	24.21		
595-THS4052IDGN	THS4052IDGN	HTSSOP-8	2	10/30	11.5	38	100	240	40.68	32.63	29.73	26.82		
595-THS4082ID	THS4082ID	SOIC-8	2	10/30	5	100	85	233	53.64	43.81	39.34	35.76		
595-OPA4820ID	OPA4820ID	SOIC-14	4	4/12.6	5.7	250	85	250	67.12	55.73	50.66	43.06		
<b>电流反馈</b>														
595-OPA683ID	OPA683ID	SOIC-8	1	5/12	2.1	1440	110	400	28.76	23.10	21.01	19.00		
595-OPA683IDBVT	OPA683IDBVT	SOT-6	1	5/12	2.1	1440	110	400	29.35	23.91	20.26	19.52		
595-OPA695ID	OPA695ID	SOIC-8	1	5/12	12.9	-	120	2900	31.36	25.18	22.95	20.64		
595-OPA695IDBVT	OPA695IDBVT	SOT-6	1	5/12	12.9	-	120	2900	30.69	24.59	22.42	20.19		
595-THS3201D	THS3201D	SOIC-8	1	6.6/15	21	-	115							