

TEXAS INSTRUMENTS 电源管理芯片

产品可能符合 RoHS 标准。在 mouser.cn 上查看 RoHS 状态。

非绝缘开关直流 - 直流稳压器 (续)

订购 500 只及以上者, 请来电询价。

贸泽电子料号	Texas Instruments 料号	封装	输入电压 (最小值)	输入电压 (最大值)	输出电压 (最小值)	输出电压 (最大值)	预设输出电压	输出电流 (最大值)	转换频率 (最大值) (kHz)	Iq (典型值) (mA)	单价			
											1	25	100	250
降压稳压器 (续)														
595-TPS54615PWP	TPS54615PWP	HTSSOP-28	6	3	6	-	-	2.5	700	11	75.10	62.36	56.69	48.13
595-TPS54672PWP	TPS54672PWP	HTSSOP-28	6	3	6	0.2	4.5	-	700	11	75.10	62.36	56.69	48.13
595-TPS54610PWP	TPS54610PWP	HTSSOP-28	6	3	6	0.9	4.5	-	700	11	75.10	62.36	56.69	48.13
595-TPS54680PWP	TPS54680PWP	HTSSOP-28	6	3	6	0.9	4.5	-	700	11	75.10	62.36	56.69	48.13
595-TPS54616PWP	TPS54616PWP	HTSSOP-28	6	4	6	-	-	3.3	700	11	75.10	62.36	56.69	48.13
595-TPS54550PWP	TPS54550PWP	HTSSOP-16	6	4.5	20.0	0.9	12	-	700	9	47.68	38.14	32.18	30.99
595-TPS54810PWP	TPS54810PWP	HTSSOP-28	8	4	6	0.9	3.3	-	700	11	81.95	59.00	49.17	42.61
595-TPS54972PWP	TPS54972PWP	HTSSOP-28	9	3	4	0.2	2.5	-	700	11	81.95	59.00	49.17	42.61
595-TPS54910PWP	TPS54910PWP	HTSSOP-28	9	3	4	0.9	2.5	-	700	11	81.95	59.00	49.17	42.61
595-TPS54010PWP	TPS54010PWP	HTSSOP-28	14	2.2	4	0.9	2.5	-	700	13	75.99	60.79	51.18	49.32
595-TPS65020RHAT	TPS65020RHAT	QFN-40	-	2.5	6	0.6	2.5	-	-	0.085	70.10	58.18	52.90	44.92
595-TPS65021RHAT	TPS65021RHAT	QFN-40	-	2.5	6	0.6	2.5	-	-	0.085	70.10	58.18	52.90	44.92
595-TPS65023RSBT	TPS65023RSBT	QFN-40	-	2.5	6	0.6	2.5	-	-	0.085	75.02	62.28	56.62	48.13
升压电荷泵稳压器														
595-TPS60243DGKT	TPS60243DGKT	MSOP-8	0.025	1.8	5.5	3	3	3	400	0.035	14.83	11.92	10.73	9.54
595-TPS60202DGSR	TPS60202DGSR	MSOP-10	0.05	1.8	3.6	3.3	3.3	3.3	450	0.055	14.83	11.92	10.73	9.54
595-TPS60204DGSR	TPS60204DGSR	MSOP-10	0.1	1.6	3.6	3.3	3.3	3.3	400	0.05	14.90	11.92	8.94	8.34
595-TPS60140PWP	TPS60140PWP	HTSSOP-20	0.1	1.8	3.6	5	5	5	450	0.06	18.63	14.90	11.92	9.91
595-TPS60210DGS	TPS60210DGS	MSOP-10	0.1	1.8	3.6	3.3	3.3	3.3	220	0.25	18.63	14.90	11.92	9.91
595-TPS60120PWP	TPS60120PWP	HTSSOP-20	0.2	1.8	3.6	3.3	3.3	3.3	400	0.04	24.59	20.04	16.76	15.12
595-TPS60110PWP	TPS60110PWP	HTSSOP-20	0.3	2.7	5.4	5	5	5	400	0.002	24.59	20.04	16.76	15.12
595-TPS60131PWP	TPS60131PWP	HTSSOP-20	0.3	2.7	5.4	5	5	5	450	0.055	25.70	20.93	18.85	15.79
升压稳压器														
595-TPS61070DDCR	TPS61070DDCR	TO/SOT-6	0.15	0.9	5.5	1.8	5.5	-	700	0.02	20.56	15.87	14.38	12.89
595-TPS61073DDCR	TPS61073DDCR	TO/SOT-6	0.15	0.9	5.5	1.8	5.5	-	700	0.02	20.56	15.87	14.38	12.89
595-TPS61004DGS	TPS61004DGS	MSOP-10	0.2	0.8	2.8	2.8	2.8	2.8	720	0.025	33.53	27.42	24.59	22.35
595-TPS61016DGS	TPS61016DGS	MSOP-10	0.2	0.8	3.3	3.3	3.3	3.3	720	0.025	36.88	30.10	27.04	24.59
595-TPS61028DRCR	TPS61028DRCR	SON-10	0.2	0.9	6.5	1.8	5.5	-	1200	0.019	23.47	18.10	16.17	14.53
595-TPS61080DRCR	TPS61080DRCR	SON-10	0.2	2.5	6	2.7	27	-	840	0.05	29.80	24.29	21.83	19.82
595-TPS61081DRCT	TPS61081DRCT	SON-10	0.35	2.5	6	2.7	27	-	780	0.05	37.55	30.62	27.49	23.10
595-TPS61025DRCR	TPS61025DRCR	SON-10	0.5	0.9	6.5	-	-	3.3	720	0.025	33.53	27.42	24.59	22.35
595-TPS61027DRCR	TPS61027DRCR	SON-10	0.5	0.9	6.5	-	-	5	720	0.025	33.53	27.42	24.59	22.35
595-TPS61020DRCR	TPS61020DRCR	SON-10	0.5	0.9	6.5	1.8	5.5	-	720	0.025	33.53	27.42	24.59	22.35
595-TPS61202DRCT	TPS61202DRCT	SON-10	0.6	0.3	5.5	5	5	5	52	45	24.21	19.37	15.50	12.89
595-TPS61200DRCT	TPS61200DRCT	SON-10	0.6	0.3	5.5	1.8	5.5	-	700	0.02	24.21	19.37	15.50	12.89
595-TPS61201DRCT	TPS61201DRCT	SON-10	0.6	0.3	5.5	3.3	3.3	3.3	700	0.02	24.21	19.37	15.50	12.89
595-TPS61026DRCT	TPS61026DRCT	SON-10	0.6	0.9	5.5	-	-	5	780	0.05	29.06	23.69	21.31	19.37
595-TPS61029DRCT	TPS61029DRCT	SON-10	0.6	0.9	5.5	1.8	5.5	-	600	0.019	29.06	23.69	21.31	19.37
595-TPS61092RSAR	TPS61092RSAR	QFN-16	0.7	1.8	5.5	-	-	5	1250	0.05	35.02	28.16	25.63	23.10
595-TPS61090RSAR	TPS61090RSAR	QFN-16	0.7	1.8	5.5	1.8	5.5	-	1200	6	35.02	28.16	25.63	23.10
595-TPS61032PWPR	TPS61032PWPR	HTSSOP-16	1	1.8	5.5	5	-	-	1200	0.19	43.81	35.16	32.04	28.91
595-TPS61030PWPR	TPS61030PWPR	HTSSOP-16	1	1.8	5.5	1.8	5.5	-	1200	6	43.81	35.16	32.04	28.91
595-TPS61030RSAR	TPS61030RSAR	QFN-16	1.8	5.5	1.8	5.5	-	3.6	700	0.02	43.81	35.16	32.04	28.91
595-TPS61032RSAR	TPS61032RSAR	QFN-16	1.8	5.5	5	-	-	3.6	700	0.02	43.81	35.16	32.04	28.91
595-UC2577T-ADJ	UC2577T-ADJ	TO-220-5	3	3	40	5	60	-	1250	0.05	188.49	169.64	155.48	136.63

双通道低压降

订购 500 只及以上者, 请来电询价。

贸泽电子料号	Texas Instruments 料号	封装	输出电流 (最大值) (A)	Vdo (典型值) (mV)	Iq (典型值) (mA)	输入电压 (最小值)	输入电压 (最大值)	输出电容器 (μF)	输出电容器类型	单价			
										1	25	100	250
595-TPS71918-12DRV	TPS71918-12DRV	SON-6	0.2	230	-	2.7	6.5	1	陶瓷	10.28	8.20	5.74	5.54
595-TPS71926-15DRV	TPS71926-15DRV	SON-6	0.2	230	-	2.7	6.5	1	陶瓷	10.28	8.20	5.74	5.54
595-TPS71928-28DRV	TPS71928-28DRV	SON-6	0.2	230	-	2.7	6.5	1	陶瓷	10.28	8.20	5.74	5.54
595-TPS71933-28DRV	TPS71933-28DRV	SON-6	0.2	230	-	2.7	6.5	1	陶瓷	10.28	8.20	5.74	5.54
595-TPS71933-33DRV	TPS71933-33DRV	SON-6	0.2	230	-	2.7	6.5	1	陶瓷	10.28	8.20	5.74	5.54
595-TPS71812-33DRV	TPS71812-33DRV	SON-6	0.2	230	0.1	2.7	6.5	1	陶瓷	10.28	8.20	5.74	5.54
595-TPS71202DRCT	TPS71202DRCT	SON-10	0.25	125	0.3	2.7	5.5	4.7	陶瓷	24.51	18.85	17.14	15.35
595-TPS71256DRCT	TPS71256DRCT	SON-10	0.25	125	0.3	2.7	5.5	2.2	陶瓷	24.51	18.85	17.14	15.35
595-TPS70851PWP	TPS70851PWP	HTSSOP-20	0.25	83	0.187	2.7	6	10	钽	36.06	28.98	26.37	23.84
595-TPS7101QD	TPS7101QD	SOIC-8	0.5	146	0.285	2.5	10	10	钽	35.31	28.83	25.85	23.54
595-TPS7101QDR	TPS7101QDR	SOIC-8	0.5	146	0.285	2.5	10	10	钽	24.21	19.37	15.50	12.89
595-TPS7150QP	TPS7150QP	PDIP-8	0.5	146	0.285	5.146	10	10	钽	24.51	18.85	17.14	15.35
595-TPS70102PWP	TPS70102PWP	HTSSOP-20	0.5	170	0.187	2.7	6	10	钽	39.71	32.41	29.13	26.45
595-TPS70151PWP	TPS70151PWP	HTSSOP-20	0.5	170	0.187	3.47	6	10	陶瓷	27.04	24.14	18.77	17.66
595-TPS70158PWP	TPS70158PWP	HTSSOP-20	0.5	170	0.187	3.47	6	10	陶瓷	49.69	40.53	36.43	30.62
595-TPS7133QD	TPS7133QD	SOIC-8	0.5	235	0.285	3.54	10	10	钽	35.31	28.83	25.85	23.54
595-TPS71025D	TPS71025D	SOIC-8	0.5	330	0.285	3.5	10	4.7	钽	30.92	24.81	22.57	20.41
595-TPS767D325PWP	TPS767D325PWP	HTSSOP-28	1	-	0.085	3.65	10	10	钽	51.85	42.39	38.07	34.57
595-PS767D301MPWPREP	TPS767D301MPWPREP	HTSSOP-28	1	-	0.085	2.7	10	10	钽	66.31	55.06	50.06	42.54
595-TPS767D318PWP	TPS767D318PWP	HTSSOP-28	1	350	0.085	3.65	10	10	钽	51.85	42.39	38.07	34.57
595-TPS767D301PWP	TPS767D301PWP	HTSSOP-28	1	350	0.085	3.65	10	10	钽	51.85	42.39	38.07	34.57
595-TPS70302PWP	TPS70302PWP	HTSSOP-24	2	160	0.195	2.7	6	22	钽	55.28	45.89	41.72	35.46
595-TPS70351PWP	TPS70351PWP	HTSSOP-24	2	160	0.195	2.7	6	22	钽	55.28	45.89	41.72	35.46
595-TPS70402PWP	TPS70402PWP	HTSSOP-24	2	160	0.195	2.7	6	22	钽	55.28	45.89	41.72	35.46
595-TPS70448PWP	TPS70448PWP	HTSSOP-24	2	160	0.195	2.7	6	22	钽	55.28	45.89	41.72	35.46
595-TPS70451PWP	TPS70451PWP	HTSSOP-24	2	160	0.195	2.7	6	22	钽	55.28	45.89	41.72	35.46
595-TPS70451PWP	TPS70451PWP	HTSSOP-24	2	160	0.195	2.7	6	22	钽	55.28	45.89	41.72	35.46

单通道低压降

订购 500 只及以上者, 请来电询价。

贸泽电子料号
