

VISHAY 整流器

产品可能符合 RoHS 标准。
在 mouser.cn 上查看 RoHS 状态。

VISHAY 肖特基整流器

一级管和整流器

Vishay Semiconductors

◆ 表面贴装设备

订购 1000 只及以上者, 请来电询价。

贸泽电子料号	Vishay料号	封装	I _{F(AV)} (A)	V _{RRM} (V)	I _{FSM} (A)	单价			
						1	10	100	500
1.0 A									
◆ 844-10BQ015PBF	10BQ015PBF	SMB	1.0	15	140	1.12	1.04	.969	.894
◆ 844-10BQ015TRPBF	10BQ015TRPBF	SMB	1.0	15	140	1.12	1.04	.991	.969
◆ 844-MBRS130TRPBF	MBRS130TRPBF	SMB	1.0	30	230	1.64	1.56	1.41	1.10
◆ 844-MBRS130LTRPBF	MBRS130LTRPBF	SMB	1.0	30	230	1.64	1.56	1.41	1.10
◆ 844-STPS1L30UPBF	STPS1L30UPBF	SMB	1.0	30	360	7.38	4.25	2.88	2.64
◆ 844-10BQ030TRPBF	10BQ030TRPBF	SMB	1.0	30	430	7.15	4.17	2.79	2.42
◆ 844-MBRA140TRPBF	MBRA140TRPBF	SMA	1.0	40	120	1.27	1.12	1.05	.946
◆ 844-1N5819	1N5819	DO-204AL	1.0	40	225	4.47	2.53	1.67	1.36
◆ 844-MBRS140TRPBF	MBRS140TRPBF	SMB	1.0	40	380	1.86	1.71	1.55	1.20
◆ 844-10BQ040PBF	10BQ040PBF	SMB	1.0	40	430	1.56	1.49	1.40	1.21
◆ 844-10BQ040TRPBF	10BQ040TRPBF	SMB	1.0	40	430	5.36	3.13	2.09	1.86
◆ 844-MBR160	MBR160	DO-204AL	1.0	60	150	.60	.522	.469	.432
◆ 844-10BQ060PBF	10BQ060PBF	SMB	1.0	60	700	2.46	2.38	1.79	1.49
◆ 844-10BQ060TRPBF	10BQ060TRPBF	SMB	1.0	60	700	6.26	3.65	2.46	2.21
◆ 844-MBR1100	MR1100	DO-204AL	1.0	100	200	.75	.671	.603	.559
◆ 844-10BQ100PBF	10BQ100PBF	SMB	1.0	100	700	1.49	1.34	1.27	1.22
◆ 844-10BQ100TRPBF	10BQ100TRPBF	SMB	1.0	100	700	4.40	2.53	1.74	1.42
◆ 844-MBRS1100TRPBF	MBRS1100TRPBF	SMB	1.0	100	870	1.49	1.42	1.24	.961
1.1 A									
◆ 844-11DQ04	11DQ04	DO-204AL	1.1	40	225	2.91	1.64	1.05	.931
◆ 844-11DQ05	11DQ05	DO-204AL	1.1	50	150	2.24	1.79	1.27	.82
◆ 844-11DQ06	11DQ06	DO-204AL	1.1	60	150	3.80	2.16	1.39	1.24
◆ 844-11DQ10	11DQ10	DO-204AL	1.1	100	85	3.73	2.09	1.37	1.18
2.0 A									
◆ 844-20BQ030PBF	20BQ030PBF	SMB	2.0	30	350	2.09	2.01	1.53	1.48
◆ 844-20BQ030TRPBF	20BQ030TRPBF	SMB	2.0	30	350	4.40	2.53	1.74	1.56
2.1 A									
◆ 844-10MQ040NPBF	10MQ040NPBF	SMA	2.1	40	120	1.04	.894	.738	.603
◆ 844-10MQ040NTRPBF	10MQ040NTRPBF	SMA	2.1	40	120	1.04	.894	.738	.603
◆ 844-10MQ060NPBF	10MQ060NPBF	SMA	2.1	60	40	1.04	.894	.738	.603
◆ 844-10MQ060NTRPBF	10MQ060NTRPBF	SMA	2.1	60	40	6.18	3.58	2.40	2.31
◆ 844-10MQ100NPBF	10MQ100NPBF	SMA	2.1	100	120	.97	.894	.82	.671
◆ 844-10MQ100NTRPBF	10MQ100NTRPBF	SMA	2.1	100	120	6.18	3.58	2.40	2.24
3.0 A									
◆ 844-30BQ015PBF	30BQ015PBF	SMC	3.0	15	650	2.24	2.16	1.64	1.34
◆ 844-30BQ015TRPBF	30BQ015TRPBF	SMC	3.0	15	650	2.83	2.68	2.09	1.64
◆ 844-15MQ040NPBF	15MQ040NPBF	SMA	3.0	40	330	1.56	1.49	1.19	.969
◆ 844-15MQ040NTRPBF	15MQ040NTRPBF	SMA	3.0	40	330	8.42	4.92	3.28	2.98
◆ 844-MBRS340TRPBF	MBRS340TRPBF	SMC	3.0	40	1580	2.61	2.53	1.97	1.64
◆ 844-30BQ040PBF	30BQ040PBF	SMC	3.0	40	2000	2.16	2.09	1.56	1.27
◆ 844-30BQ040TRPBF	30BQ040TRPBF	SMC	3.0	40	2000	14.75	9.16	6.83	5.97
◆ 844-30BQ060PBF	30BQ060PBF	SMC	3.0	60	1200	3.13	2.91	2.26	1.88
◆ 844-30BQ060TRPBF	30BQ060TRPBF	SMC	3.0	60	1200	3.28	2.98	2.38	1.97
◆ 844-30BQ100PBF	30BQ100PBF	SMC	3.0	100	800	2.83	2.68	2.11	1.72
◆ 844-30BQ100TRPBF	30BQ100TRPBF	SMC	3.0	100	800	9.46	5.81	4.42	4.10
3.3 A									
◆ 844-31DQ10	31DQ10	DO-201AD	3.3	100	210	7.90	4.54	3.05	2.84
5.0 A									
◆ 844-50SQ080	50SQ080	DO-204AR	5.0	80	1900	16.39	10.50	8.20	7.08
◆ 844-50SQ100	50SQ100	DO-204AR	5.0	100	1900	16.91	10.80	8.42	7.08
5.5 A									
◆ 844-50WQ03FNPBF	50WQ03FNPBF	TO-252AA	5.5	30	320	4.40	4.17	2.67	2.67
◆ 844-50WQ04FNPBF	50WQ04FNPBF	TO-252AA	5.5	40	340	5.07	4.84	3.11	3.11
◆ 844-50WQ06FNPBF	50WQ06FNPBF	TO-252AA	5.5	60	320	5.66	4.62	3.46	3.46
◆ 844-50WQ10FNPBF	50WQ10FNPBF	TO-252AA	5.5	100	330	7.60	7.30	4.74	4.65
7.0 A									
◆ 844-6CWQ10FNPBF	6CWQ10FNPBF	TO-252AA	7.0	100	440	14.01	9.31	6.54	6.54
7.5 A									
◆ 844-MBR735PBF	MBR735PBF	TO-220AC	7.5	35	690	4.62	4.47	4.15	3.61
◆ 844-MBR745PBF	MBR745PBF	TO-220AC	7.5	45	690	8.42	5.22	3.87	3.65
8.0 A									
◆ 844-80SQ035	80SQ035	DO-204AR	8.0	35	2400	5.81	5.59	4.44	3.62
◆ 844-80SQ040	80SQ040	DO-204AR	8.0	40	2400	14.38	11.47	8.20	7.30
◆ 844-80SQ045	80SQ045	DO-204AR	8.0	45	2400	17.14	10.95	8.49	7.08
◆ 844-8TQ100PBF	8TQ100PBF	TO-220AC	8.0	100	850	6.26	5.96	4.57	3.73
◆ 844-8TQ100SPBF	8TQ100SPBF	TO-263	8.0	100	850	8.72	8.42	7.45	6.10
◆ 844-8TQ100STRPBF	8TQ100STRPBF	TO-263	8.0	100	850	7.75	7.45	6.04	5.10
9.0 A									
◆ 844-95SQ015	95SQ015	DO-204AR	9.0	15	850	5.14	4.62	4.18	3.91
◆ 844-90SQ030	90SQ030	DO-204AR	9.0	30	2150	4.92	4.47	4.18	3.99
◆ 844-90SQ040	90SQ040	DO-204AR	9.0	40	2150	5.22	4.99	4.11	3.33
◆ 844-90SQ045	90SQ045	DO-204AR	9.0	45	2150	4.99	4.77	3.93	3.18
10.0 A									
◆ 844-STPS1045BPBF	STPS1045BPBF	TO-252AA	10	45	390	7.82	7.15	5.51	5.22
◆ 844-MBR1045PBF	MBR1045PBF	TO-220AC	10	45	1060	4.92	4.69	4.40	3.73
◆ 844-10CTQ150PBF	10CTQ150PBF	TO-220AB	10	150	620	18.77	11.99	9.39	8.12
12.0 A									
◆ 844-12CWQ03FNPBF	12CWQ03FNPBF	TO-252AA	12	30	320	7.23	6.63	5.22	4.47
◆ 844-12CWQ06FNPBF	12CWQ06FNPBF	TO-252AA	12	60	320	6.85	6.63	3.75	3.56
◆ 844-12CWQ10FNPBF	12CWQ10FNPBF	TO-252AA	12	100	330	5.74	5.44	3.45	3.45

