

VISHAY 二极管, 整流器和可控硅

产品可能符合 RoHS 标准。
在 mouser.cn 上查看 RoHS 状态。

VISHAY HEXFRED 二极管

8.0 A - 过孔

订购 1000 只及以上者, 请来电询价。

贸泽电子料号	Vishay 料号	封装	I _{FSM} (V)	V _{RMM} (V)	trr (最大值) (ns)	单价			
						1	10	100	500
844-HFA08TB60PBF	HFA08TB60PBF	TO-220AC	60	600	18	5.81	5.59	4.55	3.93

15 A - 过孔

订购 1000 只及以上者, 请来电询价。

贸泽电子料号	Vishay 料号	封装	I _{FSM} (V)	V _{RMM} (V)	trr (最大值) (ns)	单价			
						1	10	100	500
844-HFA15PB60PBF	HFA15PB60PBF	TO-247AC	150	600	19	16.09	15.27	12.22	10.65
844-HFA15TB60PBF	HFA15TB60PBF	TO-220AC	150	600	19	9.98	9.46	7.60	6.73

25 A - 过孔

订购 1000 只及以上者, 请来电询价。

贸泽电子料号	Vishay 料号	封装	I _{FSM} (V)	V _{RMM} (V)	trr (最大值) (ns)	单价			
						1	10	100	500
844-HFA25PB60PBF	HFA25PB60PBF	TO-247AC	225	600	23	27.12	23.02	18.40	17.58
844-HFA25TB60PBF	HFA25TB60PBF	TO-220AC	225	600	23	15.20	14.45	11.47	10.13

30 A - 过孔

订购 1000 只及以上者, 请来电询价。

贸泽电子料号	Vishay 料号	封装	I _{FSM} (V)	V _{RMM} (V)	trr (最大值) (ns)	单价			
						1	10	100	500
844-HFA30PA60CPBF	HFA30PA60CPBF	TO-247AC	150	600	19	22.05	21.68	16.39	14.38

VISHAY 单相桥式整流器

订购 2000 只及以上者, 请来电询价。

贸泽电子料号	Vishay 料号	封装	V _{RMM} (V)	I _{FSM} (V)	单价			
					1	10	100	500
25 A - 过孔								
844-26MB05A	26MB05A	D-34	50	420	46.79	38.22	37.32	30.69
844-26MB10A	26MB10A	D-34	100	420	43.28	36.88	34.87	29.87
844-26MB20A	26MB20A	D-34	200	420	43.51	38.22	37.32	30.69
844-26MB40A	26MB40A	D-34	400	420	49.54	42.54	39.86	34.57
844-26MB60A	26MB60A	D-34	600	420	42.84	39.04	36.36	31.07
844-26MB100A	26MB100A	D-34	1000	420	55.35	50.66	47.08	40.01
844-26MB120A	26MB120A	D-34	1200	420	43.58	39.63	38.81	31.96
844-26MT60	26MT60	D-63	600	375	94.32	78.52	73.98	65.04
844-26MT120	26MT120	D-63	1200	375	140.21	126.87	120.39	100.13
844-GBPC2502A	GBPC2502A	GBPC	200	420	21.08	18.85	16.69	14.90
844-GBPC2506A	GBPC2506A	GBPC	200	420	22.13	20.04	16.69	14.90
35 A - 过孔								
844-36MB05A	36MB05A	D-34	50	500	53.04	51.85	50.66	36.80
844-36MB10A	36MB10A	D-34	100	500	52.67	51.48	50.29	37.92
844-36MB20A	36MB20A	D-34	200	500	41.65	39.78	38.81	29.80
844-36MB40A	36MB40A	D-34	400	500	44.55	43.14	41.35	32.33
844-36MB60A	36MB60A	D-34	600	500	45.07	42.47	41.35	32.63
844-36MB80A	36MB80A	D-34	800	500	45.82	44.40	41.35	33.23
844-36MB100A	36MB100A	D-34	1000	500	52.67	51.48	50.29	38.14
844-36MB120A	36MB120A	D-34	1200	500	61.02	55.80	51.85	43.96
844-36MB160A	36MB160A	D-34	1600	500	76.96	75.25	73.46	53.42
844-36MT40	36MT40	D-63	400	500	117.41	114.73	112.05	81.50
844-36MT60	36MT60	D-63	600	500	107.06	104.60	102.14	78.60
844-36MT80	36MT80	D-63	800	500	103.78	93.94	91.86	74.13
844-36MT100	36MT100	D-63	1000	500	111.45	108.92	106.39	81.88
844-36MT120	36MT120	D-63	1200	500	109.22	98.86	91.86	78.00
844-36MT160	36MT160	D-63	1600	500	136.78	127.77	119.20	102.07
844-GBPC3504A	GBPC3504A	GBPC	400	500	21.75	18.92	17.21	14.90
844-GBPC3506A	GBPC3506A	GBPC	600	500	22.95	19.44	17.21	14.90
844-GBPC3508A	GBPC3508A	GBPC	800	500	29.50	26.67	22.13	19.15
844-GBPC3512A	GBPC3512A	GBPC	1200	500	25.11	21.61	17.58	16.17

VISHAY 相控可控硅整流器

订购 1000 只及以上者, 请来电询价。

贸泽电子料号	Vishay 料号	封装	I _{T(RMS)} (A)	V _{RMM} (V)	t _q (uS)	单价			
						1	10	100	500
25 A - 过孔									
844-25RIA40	25RIA40	TO-208AA (TO-48)	40	400	110	113.61	102.74	85.30	73.76
844-25RIA120	25RIA120	TO-208AA (TO-48)	40	1200	110	106.98	96.25	89.55	77.41
50 A - 过孔									
844-50RIA60	50RIA60	TO-208AC (TO-65)	80	600	110	121.51	94.47	78.30	72.34
844-50RIA80	50RIA80	TO-208AC (TO-65)	80	800	110	151.09	136.71	113.54	98.19
844-50RIA120	50RIA120	TO-208AC (TO-65)	80	1200	110	179.10	143.26	125.38	119.27
200 A - 过孔									
844-ST180S12P0V	ST180S12P0V	TO-209AB (TO-93)	314	1200	100	1053.36	1023.78	733.38	669.46
720 A - 过孔									
844-ST330C16C0	ST330C16C0	TO-200AB (E-Puk)	1420	1600	100	1194.16	1160.64	831.42	758.93

VISHAY 可控硅模块

订购 1000 只及以上者, 请来电询价。

贸泽电子料号	Vishay 料号	封装	V _{RMM} (V)	I _{FSM} (A)	单价			
					1	10	100	500
25 A - 过孔								
844-P102W	P102W	PACE-Pak	600	375	203.24	191.47	168.89	148.70
160 A - 过孔								
844-VSKT162/16PBF	VSKT162/16PBF	INT-A-Pak	1600	355	646.81	586.09	510.47	480.45
250 A - 过孔								
844-VSKT250-12	VSKT250-12	MAGN-A-Pak	1200	8900	1658.37	1506.61	1402.84	1291.98
844-VSKT250-16	VSKT250-16	MAGN-A-Pak	1600	8900	1730.71	1572.32	1464.00	1348.30

