

F



E

D

C




B

A


ISO VIEW
SCALE 1/1

SEE DETAIL A

SEE DETAIL B



SECTION A-A



ASSOCIATED PARTS

FEMALE TERMINALS			RANGE 1	WIRE SIZE (mm2)	TYPE	RANGE 2	WIRE SIZE (mm2)	TYPE
1.5 SICMA 3+ CLASS 150°	TINNED	MVL REFERENCE	21ICC2S1190P	0.30 ~ 0.75	1.5 X 0.8 mm			
		DELPHI REFERENCE	13602481					
2.8 SICMA 2	TINNED	MVL REFERENCE	21ICC3S2120	1.00 ~ 2.00	2.8 X 0.8 mm			
		DELPHI REFERENCE	15368841					
2.8 SICMA 3 CLASS 150°	TINNED	MVL REFERENCE	21ICC3S1190	0.35 ~ 0.75	2.8 X 0.8 mm	21ICC3S4190	0.80 ~ 1.30	2.8 X 0.8 mm
		DELPHI REFERENCE	33501947			33501951		
2.8 SICMA 3 CLASS 150°	TINNED	MVL REFERENCE	21ICC3S2190	1.00 ~ 2.00	2.8 X 0.8 mm			
		DELPHI REFERENCE	33501948					
DESCRIPTION		MVL PART NUMBER		DELPHI PART NUMBER		RSA PART NUMBER		
CAP FOR 1.5 CAVITY		210 A 01 5019		15342610		-		

PARTS LIST

REP.	QTY	DESCRIPTION	MATERIAL	COLOR	MVL P/N
5	1	MATTE SEAL	SILICON	GREEN	211 M 110
4	1	MATING SEAL	SILICON	BLUE	211 M 077
3	1	SECONDARY LOCK	PBT GF15%	YELLOW	502426-00
2	1	REAR GRID	PBT	BLACK	502428-00
1	1	6WAY FEMALE HOUSING	PBT	BLACK	502432-00

SPECIFICATION

HMC/KIA : ES 91500-00
MS 300-34 4rd Min
MS201-02
MS201-01

MVL SPECIFICATION No. : KN 05-002

Ø OF WIRE IN 1.5	MIN	1.40
	MAX	2.90
Ø OF WIRE IN 2.8	MIN	1.60
	MAX	3.60

PD15-028	-	DELPHI P/N ADDED	
PD11-142	D5	Correct character name of mold identification number	
ECN-NO. 제품 규격	POSITION 위치	CHANGE DESCRIPTION 변경 사항	
KN 05-002			
PRODUCT SPEC. 제품 규격	PACKAGING SPEC. 포장 규격	APPLICATION SPEC. 사용 규격	COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.
TOLERANCES 공차	±0.2, 2°	MATERIAL : 재질 : SEE PART LIST	SURFACE FINISH 표면 처리
COUNTERPART No. 상대품 품번	902975-00	COLOUR : 색상 : SEE DR'G	
DO NOT MEASURE DRAWING 도면을 측정하지 않것		TOOL NO. 공정 번호	ECO Loc. Code ECO 위치코드 KN
CREATED BY 작성	DATE 날짜	NAME 이름	TITLE 품명
MODIFIED BY 수정	15/02/06	BAEKHC	PROJECT 프로젝트명
CHECKED BY 검토	15/02/06	PARKJH	
APPROVED BY 승인	15/02/06	LEEMY	ESR NO. ESR 번호
FILE NAME 파일명	6WAY_FEMALE_S_LOCK.ASSY		CAT. NO. 목록 번호
			DOCUMENT UNDER PDS CONTROL NO MODIFICATION ALLOWED OUTSIDE PDS에 의해 관리되는 문서임. 외부에서 수정은 허용되지 않음.

DELPHI	CAD SYSTEM
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE NAM YANG, KOREA	pro / eng.
C	DWG SIZE 도면 크기
THIRD ANGLE 삼각법	A3
DIMENSION IN MILLIMETERS 치수단위 밀리미터	APPROVAL LEVEL 승인 수준
DRAWING NUMBER 도면 번호	REV. 개정
STATE 상태	C
PART NUMBER 제품 번호	SEE TABLE
	SHEET 도면수
	1 of 1 의
	SCALE 축척 1:1

ASSY PART NUMBER			
MVL		DELPHI	
P/N	REV.	P/N	REV.
902970-00	C	13602477	01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13602477](#)