






SYMBOL DEFINITION			MISSING SYMBOLS			DWS STATUS			ZONE	REVISION HISTORY			AUTH		DR		APVD								
						DATE	STG	REV		N/P	CHG						1	2							
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.			TOTAL NO OF INSPECTIONS REQUIRED			9	NO MISSING SYMBOL NUMBER			06JN06			R	01	-	-	WAS PE143265 AND RELEASED			281314		RH	RH	CJF	CJF
							25JA07			R	01	AA	-	-	UPDATE PDM ATTRIBUTE			400337		WHC	WHC	CJF	CJF		
			LAST NO. USED			8																			



NOTES


- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- MATERIAL RECYCLING CODE PER ISO 11469. (1.5)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.

- (1.5)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.

- CLIP TO FIT M5 STUD.



SCALE 1:1

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED		ANGULAR TOLERANCE 25°	
FROM	TO	±0.2	±0.4	±1	±1.2
> 0	> 20	±0.2	±0.4	±1	±1.2
> 20	> 30	±0.3	±0.5	±1	±1.2
> 30	> 70	±0.4	±0.6	±1	±1.2
> 70	> 100	±0.5	±0.7	±1	±1.2
> 100	> 150	±0.6	±0.8	±1	±1.2
> 150	> 200	±0.7	±0.9	±1	±1.2
> 200	> 250	±0.8	±1.0	±1	±1.2
> 250	> 300	±0.9	±1.1	±1	±1.2
> 300	> 400	±1.0	±1.2	±1	±1.2

THIRD ANGLE PROJECTION		DO NOT SCALE		USE MATH DATA	
1		1		1	

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WYOMING, OH	
DRAWING NAME MOUN CLIP CONN	
DRAWING NUMBER 13589755	
SIZE A0	
SCALE 5:1	
FRAME NO 1 OF 1	
SHEET NO 1 OF 1	
STG R	
REV 01	
N/P AA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13589755](#)