






SYMBOL DEFINITION				MISSING SYMBOLS		DWG STATUS		ZONE		REVISION HISTORY		AUTH		DR		APVD		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.				TOTAL NO OF INSPECTIONS REQUIRED		48	NO MISSING SYMBOL NUMBER		DATE		STG	REV	N/P	CHG	1 2			
							03JUL06		R	01	-	-	RELEASED		282408		JWG	TJW
				LAST NO. USED		19			28DE06		R	01	AA	-	-	REDRAWN TO PD		288246



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CONN 13594406
SEAL 13594408
 - THIS PART USED IN ASSEMBLY 13594404

DWG TYPE PART DRAWING	
STYLE	
VOLUME 10/1 0.524	DISTR CODE D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS NOTED IF THE IN SCHEMA DIMENSIONS AND TOLERANCES ARE NOT SHOWN, SEPARATE NOTATIONS OF REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	
DO NOT SCALE	
USE MATH DATA	
TOLERANCE UNLESS OTHERWISE SPECIFIED DIMENSIONAL RANGE (MM) FROM TO TOLERANCE > 0 > 30 > 70 > 100 > 150 > 200 > 250 > 300 > 400 ±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2 ANGULAR TOLERANCE ±1	

DELPHI						
DELPHI PACKARD ELECTRIC SYSTEMS WILSON, OH						
DR	DATE					
AP/D1 JIANWEI GUO	03JL06					
AP/D2 YA JUN WU	03JL06					
AP/D3 JIANWEI GUO	03JL06					
AP/D4						
AP/D5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
WATERLOO W4629006 PBT 6F20 YEL						
DRAWING NAME LOCK TPA/CLIP YEL						
DRAWING NUMBER 13594407						
SIZE A0	SCALE 5:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1	STG R	REV 01	N/P AA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13594407](#)