

MODLINK MSDD SOCKET INSERT USA 2XNEMA 5-15

GFCI 125VAC/15A

Art.No.: 4000-68000-3220000

Weight: 0.124

Country of origin: CN

Model designation: Fr.Modul-AB-125-15-GFCI-SC

USA (2× NEMA-GFCI 5-15)

(Ground Fault Circuit Interrupter)

Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	https://shop.murrelektronik.com/4000-68000-3220000
GTIN	4048879037280
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-08-22

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

ETIM-7.0	EC000020
ETIM-8.0	EC000020
EAN	4048879037280

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	27 mm

Environmental characteristics | Climatic

Storage temperature min.	-40 °C
Storage temperature max.	70 °C

USA

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	yes
Connection cross section max.	6 mm ²
AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[4000-68000-3220000](#)