


REV.	DATE	DESCRIPTION
NC	12/08/97	INITIAL RELEASE
A	09/24/06	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex							
7						DRAWN	G.R.S.	09/24/06									
6						CHECKED											
5						ISSUED				PART DESCRIPTION							
4	CONTACT PIN (M)	BRASS	GOLD	1		DO NOT SCALE DRAWING	SHEET	1 OF 1		SMA "T" ADAPTER JACK–PLUG–JACK							
3	CONTACT PIN (F)	BER. COPPER	GOLD	2	PART NO.												
2	INSULATOR	TEFLON	NATURAL	1	132217												
1	BODY	BRASS	GOLD	1	CAD FILE			DWG. NO.		132217.DWG		REV.	A	SIZE	A	SCALE	NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[132217](#)