





PART NUMBER	NO. OF MOD.
10026155-005	1
10026155-005LF	






NOTES:

- ① BODY MATERIAL: LIQUID CRYSTAL POLYMER 30% GLASS.
FLAME RETARDANT ACC. TO UL 94-V0.
COLOR: NATURAL
2. FOR LEAD FREE NUMBERS, ADD AN 'LF' SUFFIX. PART NUMBERS THAT DO NOT END IN 'LF' ARE LEAD FREE.
EXAMPLE: 10026155-005LF
3. THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF AND THE NONE LF PART NUMBERS MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
4. ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOUR PHASE REFLOW OVEN.

VIEW D
OPTIONAL GEOMETRY

mat'l. code SEE NOTE 1				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family METRAL (tm)	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
A	V03-0335	LP	03/21/03	angles	.X±.3	MM	4 ROW SHROUD	
B	V03-0439	LP	4/22/03	linear	.XX±.13			
C	V06-0080	JRV	3/15/06	0°±2°	.XXX±.051	scale 1:1		
D	V06-0609	DCH	2008-06-22	dr	L.POTTEIGER 03/21/03			
				enr	M.GRAY 03/21/03		dwg no 10026155 sheet 1 of 2 size A4	
				chr	M.GRAY 03/21/03			
				app	M.GRAY 03/21/03		type CUSTOMER Drawing	
sheet index	revision sheet	D	D					
		1	2					

PART NUMBER	DIM A	DIM B	NO. OF MOD.
10026155-001	35.95	34.00	3
10026155-002	23.95	22.00	2
10026155-003	47.95	46.00	4
10026155-004	95.95	94.00	8
10026155-001LF	35.95	34.00	3
10026155-002LF	23.95	22.00	2
10026155-003LF	47.95	46.00	4
10026155-004LF	95.95	94.00	8



mat'l. code	SEE NOTE 1	surface	ASME Y14.5	tolerance	ASME Y14.5	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified			METRAL (tm)
D				angles	.X±.3	MM	4 ROW SHROUD
				0°±2°	.XX±.13	scale 1:1	
				dr	L.POTTEIGER 03/21/03		dwg no
				enr	M.GRAY 03/21/03		sheet 2 of
				chr	M.GRAY 03/21/03		10026155
				app	M.GRAY 03/21/03		size
sheet	revision						A4
index	sheet						type
							CUSTOMER Drawing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10026155-001LF](#) [10026155-002](#) [10026155-002LF](#) [10026155-003](#) [10026155-003LF](#) [10026155-004](#) [10026155-004LF](#) [10026155-005](#) [10026155-005LF](#) [10026155-001](#)