



PRODUCT NUMBER

10129463-XXXLF



MATERIALS:

HOUSING—HIGH TEMP. THERMOPLASTIC
BLACK COLOR, UL94V-0.

CONTACTS —COPPER ALLOY
50u" Ni OVERALL UNDERPLATING.
PLATED WITH HARD GOLD ON CONTACT AREA
AND GOLD FLASH IN SOLDER AREA.

SHIELD—COPPER ALLOY,
PLATED WITH NICKEL.

THE PART IS CAPABLE TO REFLOW SOLDERING PROCESS.


PART NUMBER SCHEME:

10129463 - XXX LF




OPTIONAL PLATING CODE:



030: 30u" Au

050: 50u" Au



Recommended PCB Layout
Tolerance: ±0.05mm
(For 1.6mm Thickness)



mat'l. code				surface	tolerance	projection	product family			
ltr	ecn no	dr	date	tolerances unless otherwise specified		 MM scale	title			
A		TAI	2015-04-30	angles	X.X±0.25 X.XX±0.13 X.XXX±0.05		10 POS. RIGHT ANGLE SHIELDED PCB JACK			
				Linear						
				dr	KENNY TAI	2014-03-18		dwg no		sheet 1 of 2
				enr	KENNY TAI	2014-03-18		10129463		size
				chr	KENNY TAI	2015-04-30				A4
				appd	PM ZHENG	2015-04-30		type		CUSTOMER Drawing
sheet index	revision sheet	A	A							
		1	2							

Printed: Jun 01, 2015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10129463-030LF](#)