




PRODUCT NUMBER
58336-XY(LF)



NOTES:

1. FOR DIM A, AND B SEE SHEET 2 AND UP.
2. BODY MATERIAL: LIQUID CRYSTAL POLYMER 30 % GLASS. FLAME RETARDANT ACC. UL 94-V0.
3. PIN MATERIAL: PHOSPHOR BRONZE.
4. PLATING: SEE DRAWING C-8626-000P
5. PRODUCT MARKING: ERICSSON PART NUMBER & BATCH I.D.
6. ALL PRODUCTS WITH PART NUMBERS SHOWN IN SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES. IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P" WILL BE ADDED TO THE END OF THE PART NUMBER. EXAMPLE: XXXXX-XXXP or XXXXX-XXXPLF

GENERAL CHARACTERISTICS AND ROHS INFORMATION:
SEE DRAWING C-8626-000P




TIN LEAD PART NUMBER:
58336-XY

LEAD FREE PART NUMBER:
58336-XYLF

YY DEFINITION: SEE SHEET 3

PLATING IN CONTACT AREA	
DASH NUMBER	PERFORMANCE LEVEL
3YY or 3YYLF	IEC CLASS I
7YY or 7YYLF	ERICSSON SPECIAL


rev	ecn no	dr	date
A	VI2084	TAB	2001/08/30
B	LS2157	SPE	2002/12/10
C	LS05-0065	JTA	2005/08/02
D	LS06-0084	LGO	2006/06/30
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		 mm		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	S.PERRICHOT	2002/03/13	ANGULAR	LINEAR	0.X ±0.3		size A4	Scale 1:1			
Eng	PH.LEGARE	2002/03/13			0.XX ±0.1						
Chr	PH.LEGARE	2002/03/13			0°.xxx ±0.05						
Appr	PH.LEGARE	2002/03/13	Product family		METRAL		Spec ref		LS06-0084		
			METRAL POWER HEADER				58336C			Rev. D	
			I MOD, 4 ROW PRESS-FIT								
			catalog no				CUSTOMER COPY			sheet 1 of 3	

REV F - 2006-04-17



Copyright FCI.



KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
P01	6.50	4.30
P03	8.00	4.30

REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION



Copyright FCI.

www.fciconnect.com			surface ISO 1302	✓	tolerance std ISO 406 ISO 1101	projection A4	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	S.PERRICHOT	2002/03/13	ANGULAR	LINEAR	0.X ±0.3	size	Scale 2:1
Eng	PH.LEGARE	2002/03/13			0.XX ±0.1	ECN	LS06-0084
Chr	PH.LEGARE	2002/03/13	0° ±2°		0.XXX ±0.05	Spec ref	
Appr	PH.LEGARE	2002/03/13	Product family		METRAL		
FCI			Title			dwg no	Rev.
			METRAL POWER HEADER			58336C	D
			I MOD, 4 ROW PRESS-FIT				
			catalog no			CUSTOMER COPY	sheet 2 of 3

REV F - 2009-04-17






Copyright FCI.

REV F - 2009-04-17

METRAL P/N	ERICSSON P/N	DIM "A"	DIM "B"	ROW	CONTACT CODE MOD. I	
					1	2
58336-X01	RPV 638 1121	6.50	4.30	D	P01	P01
		6.50	4.30	C	P01	P01
		8.00	4.30	B	P03	P03
		6.50	4.30	A	P01	P01

METRAL P/N	ERICSSON P/N	DIM "A"	DIM "B"	ROW	CONTACT CODE MOD. I	
					1	2
58336-X02	RPV 638 1127	6.50	4.30	D	P01	P01
		6.50	4.30	C	P01	P01
		6.50	4.30	B	P01	P01
		6.50	4.30	A	P01	P01

www.fciconnect.com			surface ISO 1302		<input checked="" type="checkbox"/>	tolerance std ISO 406 ISO 1101		projection 	mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	S. PERRICHOT	2002/03/13	ANGULAR	LINEAR	0.X		±0.3		size A4	Scale 1:1
Eng	PH. LEGARE	2002/03/13			0.XX		±0.1			
Chr	PH. LEGARE	2002/03/13	0° ±2°		0.XXX		±0.05		ECN	LS06-0084
Appr	PH. LEGARE	2002/03/13	Product family				METRAL	Spec ref		
			Title METRAL POWER HEADER I MOD, 4 ROW PRESS-FIT				dwg no 58336C		Rev. D	
catalog no							CUSTOMER COPY		sheet 3 of 3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[58336-101LF](#)