




CURRENT RATING 1.5 A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE 500V AC (CONT / CONT)

OPERATING TEMPERATURE -55°C TO 125°C

CONTACT RESISTANCE 20 mΩ MAX

INSERTION FORCE :0.75 N MAX /CONT

EXTRACTION FORCE: 0.15 N MIN /CONT

INSULATION RESISTANCE : 10^4 M Ω MIN

NOTES

LEAD FREE INDICATOR : LF- LEAD FREE

1.  PERFORMANCE LEVEL INDICATOR
(REF DWG No. BSC/201844.003)
2. THIS PRODUCT IS CSA APPROVED
THIS PRODUCT IS UL RECOGNISED
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING: BSA, 201.572001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVE
AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.



STATUS: **Released**

¹¹ Printed: Mar 15, 2011.

					Material		Spec ref			
					Mat code		✓			
					Heat treat		tolerance H9/D9 ± 0.05 H8/D8 ± 0.03 H7/D7 ± 0.02		projection 	
					Drawing/Finish					
rev		ecn no	dr	date	In		J V B		size	
1		00000000	ION	14-1-91	Eng		Product family		A1	
2		105-0093	MEH	06/06/05	Cdr		Model Name		ECN	
3		3026-0256	Gus.M	03/08/05	Appr		Model Revision		REL Level	
4		3026-0297	Kasson	07/09/06						
5		0297-0262								
6		0290-0010	NZ	2010/03/29						
							MPACS 5+2R RA RCP CONN TYPE A		2 BS.C.201418,029	
					title		HMPR01PASIF01----- CUSTOMER DRAWING		sheet 1 of 1	
					Proj/E file		catalog no		F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM2R01PA510FN9LF](#)