




DIMENSIONS mm (inches)



METHOD OF INSERTION
ON THE PCB = FLAT ROCK



PCB DRILLING



PART NUMBER	8609			81		7		5	
PIN OUT									
rows a-b-c				3				96	
rows a-c				4				64	
NUMBER OF CONTACTS									
TERMINATION									
L = 13.10 ±0.20 (.515)									96
L = 17.10 ±0.20 (.673)									97
PERFORMANCE CLASS									
DIN 41612 class 3									4
DIN 41612 class 2									6
DIN 41612 class 1									0
TERMINATION TYPE									
TIN LEAD									000A
LEAD FREE									ALF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000C

European Views

www.fciconnect.com	surface ISO 1302	<input checked="" type="checkbox"/>	tolerance std ISO 406 ISO 1101	projection mm	mm
TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	ROUILLARD	1993/06/16	ANGULAR	0.X	±0.1
Eng	TARON	1993/06/16	LINEAR	0.XX	±0.1
Chr	LEGARE	1993/06/16	0.XX' ±2'	0.XXX	±0.1
Appr	LEGARE	1993/06/16	Product family	DIN 8609	Spec ref -

rev	ecn no	dr	date
-	-	MAS	1999/08/05
F	LS05-004	JTA	2005/02/28
G	LS06-0095	LGO	2006/06/17
-	-	-	-
-	-	-	-
-	-	-	-

FCI title STRAIGHT FEMALE - STYLE C
PRESS FIT REAR PLUG UP
catalog no -

size A3 Scale 1.5
ECN LS06-0095

dwg no C-8609-0366
CUSTOMER sheet 1 of 1

Rev. 6



Copyright FCI.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86093968196745ALF](#) [86093968196755ALF](#) [86093968196765ALF](#) [86094648196755ALF](#) [86094648196765ALF](#)
[86094648197755ALF](#) [86093968197755ALF](#) [86094648197765ALF](#) [86093968197765ALF](#)