





A



VIEW WITHOUT BOARDLOCK




B



C

LAYOUT DIMENSIONS (after plating)
CONNECTOR SIDE VIEW






D

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8639-0001

European Views

rev	ecn no	dr	date
B	-	DEB	2003/09/18
C	LS05-001	MPE	2005/03/10
D	LS06-0095	LGO	2006/07/18
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JOUBERT	2002/09/03	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	2002/09/03			0.XX	±0.1				
Chr	LEGARE	2002/09/03			0.XXX	±0.1				
Appr	LEGARE	2002/09/03	0.XX' ±2°				ECN		LS06-0095	
			Product family				D-SUB		Spec ref -	
			title SOCKET CONNECTOR 3W3 WITH POWERS CONTACTS				dwg no C01-8639-1992		Rev. D	
			catalog no -				CUSTOMER		sheet 1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[DA3W3S500M40LF](#)