







FCIconnect.com

Copyright FCI




LEAD FREE PART NUMBER


SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.GX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24A.GX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24A.GX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24A.GX00LF

Plating: 4 --> Flash Au
Plating: 6 --> 0.76µ Au

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATION:
SEE DRAWING C01-8646-0000

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D—SUB											
ltr	ecn no	dr	date	tolerances unless otherwise specified						title FEMALE DELTA—D STRAIGHT , SOLDER TYPE											
J	ELX-I-21654	AB	2015-10-26	angles	linear	.0±.0.1														scale 2:1	
						.00±0.1															
						.000±0.1															
				0°±2°																	
				dr	JOUBERT		1996-09-10				dwg no						sheet 1 of 1		size		
				engr	ALIAS BABU		2015-10-26				C01—8646—0495						A3				
				chr	MITHUN PAUL		2015-10-26														
				appd	BIJU K PAUL		2015-10-26														
sheet index		revision sheet		J	1																

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[D09S24A4GX00LF](#) [D09S24A6GX00LF](#) [D15S24A4GX00LF](#) [D15S24A6GX00LF](#) [D25S24A6GX00LF](#)
[D37S24A4GX00LF](#) [D37S24A6GX00LF](#) [D25S24A4GX00LF](#)