

A

B

C



D

A

B

C

D



Tie-rip



MATERIAL:

Thermoplastic

TEMPERATURE RANGE:

-Climatic category -55° / +125°

PACKAGING:

Per 100 pieces

COLOUR

Black

NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in 65-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see 65-14-920.

Dimensions are in millimeters

Shell size	Number of contacts	A $+0.9$ -0.2	B $+0.10$ 0	C ± 0.05	D ± 0.10	E ± 0.10	F ± 0.10	G ± 0.10	PART NUMBER
E	09	30.60	12.50	24.99	19.00	10.50	9.90	18.20	86305002BLF
A	15	38.90	12.50	33.32	20.60	12.50	9.90	22.80	863026BLF
B	25	52.80	12.50	47.04	23.60	17.00	9.90	29.40	863027BLF
C	37	69.10	12.50	63.50	29.00	24.00	9.90	37.00	863028BLF
D	50	66.70	15.30	61.11	28.00	24.00	12.70	35.00	863029BLF

European Views

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection ISO 1101	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	JOUBERT	1999/01/04	ANGULAR	0.X	± 0.1
Eng	PESSON	1999/01/04	LINEAR	0.XX	± 0.1
Chr	LEGARE	1999/01/04	0.XX' ± 2'	0.XXX	± 0.1
Appr	LEGARE	1999/01/04	Product family D-SUB		
		Spec ref -		size A3	Scale 5
				ECN LS08-0186	
				Rev. H	
				catolog no -	
				CUSTOMER sheet 1 of 1	

rev	ecn no	dr	date
B	LS05-0026	MPE	2005/07/08
C	LS05-0084	MPE	2005/09/29
D	LS06-0095	LGO	2006/07/24
E	LS07-0249	MPE	2007/10/02
F	LS07-0258	LGO	2007/10/16
G	LS08-0146	MPE	2008/06/16
H	LS08-0186	MPE	2008/09/04



POTTING PLASTIC HOODS
right angle exit

01-8655-1523

Rev. H

REV F - 2006-04-17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[863027BLF](#) [863026BLF](#) [863028BLF](#)