



JKL PART NUMBER	LENGTH A +/- 2mm	COLOR (REF.)	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF4183-20B	183mm	RGB HIGH OUTPUT WHITE 5600° KELVIN	900 @ 0°C	365	5 ± 1	15,000±10%	20,000
BF4220-20B	220mm		1,000 @ 0°C	405	5 ± 1	15,000±10%	20,000
BF4418-20B	418mm		1,400 @ 0°C	765	5 ± 1	15,000±10%	20,000

*NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION				
			TITLE SINGLE LEAD TIPLESS MINIATURE FLUORESCENT LAMP						
DRAWN BY L. WENGSTROM			APPVD BY DATE J.K. 9/17/02		SIZE A	FSCM NO. 55335	DRAWING NO. BF 4-20B		
RELEASED TO CAD 9/17/02			- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	RELEASED DATE 9/17/02	REVISION DATE	REV. NO.	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF4418-20B](#)