


JKL LAMP PART NUMBER	COLOR 6900°KELVIN	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mArms)	BRIGHTNESS (Cd/m2)	*RATED LIFE (HRS)
CF20277-28B	x = .325 y = .295	1560 @ 0°C	625 @ 5mA	5.0 TYP.	38,000 TYP.	20,000 MIN. 40,000 AVG.

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OFTHE INITIAL RATING.

			METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION						
				DRAWN BY L. WENGSTROM	APPV'D BY J.K.	DATE 4/22/04	SIZE A	FSCM NO. 55335	DRAWING NO. CF20277-28B			
RELEASED & CANCEL P-0404-13			4/22/04		- CAD DRAWING -		SCALE NONE		RELEASED DATE 4/22/04	REVISION DATE	REV. NO.	SHEET 1 OF 1
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE		MANUAL REVISIONS NOT PERMITTED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[CF20277-28B](#)