

Mallory			Mallory Sonalert Products, Inc.		Part #: JT028-YG-CSL	
Sales Outline Drawing				Revision: C		
Specifications:						
Stack Number:	1	2				
LED Color:	YELLOW	GREEN				
Connection Wires:	Yellow and Brown	Green and Brown				
LED Current Draw:	<60 mA	<40 mA				
Rated Voltage:	24 VAC/DC					
Operating Voltage:	20-28 VAC/DC					
Sound Level Category:	Loud	Loud	Loud	Loud		
Mode of Operation:	Continuous	Medium Pulse (5PPS)	Double Pulse (0.5PPS)	Continuous for 5 sec then 0.1s beep until reset		
Connection:	Black and Gray Wires	Black and Gray Wires; Orange wire connected to	Black and Gray Wires; Purple wire connected to Green/Yellow wire	Black and Gray wires; Orange and Purple wires connected to Green/Yellow wire		
Sound Current Draw:	40mA Max.	40mA Max.	40mA Max.	40mA Max.		
Loudness @ 1m:	80-85 dB(A) Typ.					
Frequency:	2000 ± 500 Hz					
Total Max Current:	<140mA with all LED's and sound unit working					
Operating Temperature:	-25° ~ +60°C					
Lens Color:	Opaque White					
Material:	ABS FR15U					
Mounting Method:	Stainless Steel Pole					
Weight Typical (g):	685					
NEMA 12:	Approved					
Options:	Please contact factory.					
Dimensions: Inches (mm)		cUL Recognized		ROHS Compliant		
		PATENT NUMBER 10309594				
LED OPERATION:		CONNECT STACK COLOR WIRE TO POWER AND BROWN WIRE TO POWER.				
SOUND OPERATION:		CONNECT GRAY AND BLACK WIRES TO POWER FOR CONTINUOUS SOUND. FOR MEDIUM PULSE, CONNECT GRAY & BLACK TO POWER AND ORANGE WIRE TO GREEN/YELLOW WIRE. FOR DOUBLE PULSE, CONNECT GRAY & BLACK TO POWER AND PURPLE WIRE TO GREEN/YELLOW WIRE. FOR CONT/BEEP, CONNECT GRAY & BLACK TO POWER AND ORANGE & PURPLE TO GREEN/YELLOW WIRE.				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[JT028-YG-CSL](#)