

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0367590027

Status:

Active

Overview:

MLX Power Connectors

Description:

6.35mm Pitch MLX Power Connector Header, 2.13mm Contact Diameter, Vertical, with Plastic Polarizing Peg, 15 Circuits, Lead-Free, Black

Documents:	
3D Model	Packaging Specification PK-43255-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-43255-003-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PSX-42002-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

UPC

PCB Headers

43255

Board-to-Board, Power, Wire-to-Board

High Vibration Application

MLX Power Connectors

MLX

884982491120

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

15

15

Black

50

No

94V-2

No

Yes

Yes

Phosphor Bronze

Tin

Tin

Nylon

3

Vertical

4.30mm

Yes

Yes

1.60mm

Tray

6.35mm

6.35mm

Yes

Yes

Fully

No

No

-55° to +105°C

Through Hole

Electrical



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[43255](#) Series

Mates With

[42021](#) MLX Power Crimp Housing Plug, [42023](#) MLX Crimp Terminal, [42024](#) MLX Crimp Terminal

Current - Maximum per Contact20.0A, 9.0A

Voltage - Maximum600V

Material Info

Reference - Drawing Numbers

Packaging SpecificationPK-43255-001-001, PK-43255-003-001

Product SpecificationPSX-42002-0001-001

Sales DrawingSDA-43255-00XX

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[36759-0027](#)