

BU-32603-@
(Shrouded Banana Plug)



- Mueller's BU-32603-@ is a shrouded Banana plug that is field assembled and is IEC 1010 compliant Banana plug.
- Fits 4mm Banana jacks that accepts shrouded Banana plugs.
- Easy Solder connection with wire between 18-14 AWG.
- Material:
 - Housing – Nylon
 - Contact – Nickel plated Brass and Beryllium Copper
- Ratings:
 - 20 Amps
 - 1000 V Cat III
 - 1500 V Cat II
- Color: The "@" in the model number represents color. Available colors:
 - 0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- RoHS 3 Compliant



Assembly Photo (Wire not included)

- 1) Slide threaded nut, and strain relief onto wire
- 2) Solder wire to banana plug
- 3) Assemble all parts and thread nut into shroud

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-32603-2](#) [BU-32603-0](#)