

BU-34 Series

(Micro Alligator Clip with Smooth Jaws)



BU-34 / BU-34X



BU-34C / BU-34M

- The BU-34 series of clips are micro alligator clips with smooth jaws. Compatible with Mueller-brand BU-36 flexible PVC insulators.
- Overall length 1.09" (27.8mm), overall width 0.20" (5.1mm), overall height 0.31" (7.9mm), maximum jaw spread = 0.22" (5.6mm)
- Connects to wire up to 18 AWG via solder or crimp connection.
- Ratings: Current 5 Amps
- The BU-34 is sold under the following models:

BU-34	Nickel-plated steel clip
BU-34X	Stainless-steel clip, use stainless-steel flux for solder connection
BU-34C	Solid copper clip
BU-34M	Solid copper marine clip with stainless hardware, lasts up to five times longer than traditional copper/steel clips in highly corrosive marine/coastal environments
- RoHS 3 compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-34C](#) [BU-34X](#) [BU-34M](#)