



NC4MX-TOP

4 pole male cable connector, TRUE OUTDOOR PROTECTION (TOP), gold contacts

The X-TOP series is a "heavy-duty" XLR cable connector for outdoor use. Outdoor protected by mating with related cable connector of the XLR TOP range (IP65).

Gold contacts are standard.

Features & Benefits

- Heavy-duty sealed XLR connector range for harsh and demanding environment
- Outdoor protection according to IP65
- Uses high impact UV resistant materials
- IEC 61984 certified

Technical Information

Product	
Title	NC4MX-TOP
Connection type	XLR
Gender	Male

Electrical	
Contact resistance	$\leq 3\text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10\text{ G}\Omega$ (initial)
Rated current per contact	10 A
Rated voltage	50 V

Mechanical	
Cable O.D.	5.0 – 8.0 mm
Insertion force	$\leq 20\text{ N}$
Withdrawal force	$\leq 20\text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	$< 2.5\text{ mm}^2$
	16 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Bushing	UV-resistant rubber
Contact plating	Gold (Au) over Nickel (Ni)
Contacts	Brass
Insert	Polyamide
Locking element	St3K32 (latch) / Ck 67 (spring)
Shell	Zinc diecast
Shell plating	Nickel
Strain relief	Polyacetal
Sealing jacket	UV-resistant rubber

Environmental	
Flammability acc. to UL94	V-0 (insert)
Standard compliance	IEC 61076-2-103
Protection class acc. IEC 60529	IP65 (mated)
Solderability acc. to	IEC 60068-2-20
Temperature range	-30 °C to +80 °C
Pollution degree acc. to IEC 60664-1	II

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Neutrik:

NC4MX-TOP