

RC3FDL

3 pole female XLR receptacle with solder lugs



Article Variations

Article Name	Details	Packaging
RC3FDL	Nickel plated housing, tin plated contacts	
RC3FDL-B	Black plated housing, gold plated contacts	

Technical Information

Product	
Title	RC3FDL
Connection Type	XLR
Gender	female

Electrical

Insulation Resistance	>1 GΩ
Contact Resistance	≤5 mΩ
Rated Current	≤10 A

Mechanical

Lifetime	>1000 Mating Cycles
Insertion Force	≤20N
Withdrawal Force	≤20N

Material

Ground Contact	Bronze
Jack	Bronze
Housing	Zinc
Latch	Steel
Spring	Steel
Plastic Body	PA6+30%GF
Ground Contact	Tin and Cer
Jack	Tin and Cer
Housing	Nickel Plating
Latch	Nickel Plating

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RC3FDL](#) [RC3FDL-B](#)