



RLS4MPZ

4 pole loudspeaker receptacle, D-Size front mounted,
3/16" flat tabs contacts

Article Variations

Article Name	Details	Packaging
RLS4MPZ	3/16" flat tabs contacts	BULK

Technical Information

Product	
Title	RLS4MPZ
Connection Type	Loudspeaker Connectors

Electrical

Rated current	continuous 30 A rms
Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$> 1 \text{ G}\Omega$
Dielectric strength	4 kV dc
Rated Voltage	250 V

Mechanical

Lifetime	> 1000 mating cycles
Chassis shape	D
Wiring	flat tab ($4.8 \times 0.5 \text{ mm}$) or soldering
Mounting direction	Front mounting or rear mounting

Material

Contact	Bronze
Contact plating	Ag
Shell	PA6+30%GF

Environmental

Temperature range	$-30 \text{ }^{\circ}\text{C}$ to $+80 \text{ }^{\circ}\text{C}$
Flammability	UL94 V-0
Solderability	complies with IEC68-2-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RLS4MPZ](#)