






DESCRIPTION: RJ-45 TO 9-POSITION MALE D-SUB — PLASTIC & METALIZED PLASTIC

MATERIAL:

HOOD: ABS UL 94V-HB




RJADK09P70808Y1

SERIES _____
POSITIONS _____
09
GENDER _____
P = MALE
D-SUB TERMINALS _____
7 = CRIMP & POKE (CONTACTS PRE-CRIMPED)
MODULAR POSITIONS _____
08
MODULAR POSITIONS LOADED _____
08
COLOR _____
1 = BLACK
2 = METALIZED (SHIELD RATING: 60dB)
3 = GRAY
D-SUB CONTACT PLATING _____
1 = GOLD FLASH
3 = 10u" DSUB CONTACT // 50u" RJ-45 CONTACT

RJ45

1. BLUE
2. ORANGE
3. BLACK
4. RED
5. GREEN
6. YELLOW
7. BROWN
8. WHITE

DB-09M



FRONT VIEW

UNITS = inch



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

DATE:
05-17-07

NorComp

SCALE: **N.T.S.** SHEET **1** OF **1** REV **2**
DWG NO. **RJADK09P70808Y1**

DO NOT SCALE FROM DRAWING

RoHS COMPLIANT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[RJADK09P7080821](#) [RJADK09P7080811](#) [RJADK09P7080831](#)