

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PLT3EH-NB	.50 (12.7)	3.3 (83.8)	.075 (1.9)	.500 (12.7)	.409 (10.4)	.40 (10.2)	0.78 (19.8)	12.2 (310)	250 (1112)	EXTRA HEAVY	2.0 (918)
PLT5EH-NB	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.500 (12.7)	.409 (10.4)	.40 (10.2)	0.78 (19.8)	19.8 (503)	250 (1112)	EXTRA HEAVY	3.1 (1425)
PLT6EH-NB	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.500 (12.7)	.409 (10.4)	.40 (10.2)	0.78 (19.8)	21.8 (554)	250 (1112)	EXTRA HEAVY	3.6 (1632)

NOTES:

*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

							TITLE				
							PAN-TY [®] NON-RELEASABLE NO-BUCKLE LASHING TIES				
							CONTROL DRAWING				
03	4/22/21	BWG	MPH	JADE	REVISED "E" DIMENSION	099443/00	ITEM REVISION NAME				
---	----	---	---	---	ADDED TOLERANCE TO DIM A & B ±.01(.25)	---	SS-27169_01/AB				
---	----	---	---	---	CORRECTED LOGO, ACTUAL TO PART	---	DATASET FILE NAME				
---	----	---	---	---	CHANGED MIN BUNDLE DIA FOR PLT3/5/6EH TO .50(12.7), WAS 1.00(25.4)	---	SS-27169_r03				
02	3/22/04	JABO			REMOVED PLT2EH-NB, INACTIVE	27169/02	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	.x ± .1 (2.5) .xxx ± .010 (.25) .xx ± .02 (.5) ANGLES ± -----				
							THIRD ANGLE PROJECTION				
							DRAWN BY MIP DATE 7-30-98 CHK MDS SCALE NONE				
							SHT 1 OF 1				
							SIZE A				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLT6EH-NB-C0](#) [PLT3EH-NB-C0](#) [PLT5EH-NB-C0](#)