


Technical drawing of a mechanical part, likely a bracket or support, showing a side view (A-A) and a front view (D-D). The side view shows a curved top with a vertical support and a base. The front view shows a rectangular base with two vertical supports. Dimensions are given in inches and millimeters.

Dimensions:

- Overall height (Side View): 0.885 (22.48) REF
- Overall width (Front View): 0.325 (8.26) REF



FRONT VIEW  
"A-A"

1. SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, MATERIAL AND COLOR.
2. PARTIAL SECTION ON FRONT VIEW IS SHOWN FOR CLARITY.

CAD FILENAME/LAYERS

# PANDUIT

CORP.

TINLEY PARK, ILLINOIS

PMCC38H25  
PUSH MOUNT CORD CLIP

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X)  $\pm 0.05$  (.3) (.XXX)  $\pm 0.010$  (0.25)  
(.XX)  $\pm 0.02$  (0.5) ANGLES  $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY CBI

**MAT'L:**

|       |      |
|-------|------|
| SCALE | NONE |
|-------|------|

|      |             |
|------|-------------|
| DATE | 3 - 13 - 96 |
|------|-------------|

NYLON

DRAWING NO.  
GB0239DA

DWG  
A  
SIZE

|     |          |     |      |                                   |          |      |     |      |  |
|-----|----------|-----|------|-----------------------------------|----------|------|-----|------|--|
|     |          |     |      |                                   |          |      |     |      |  |
|     |          |     |      |                                   |          |      |     |      |  |
|     |          |     |      |                                   |          |      |     |      |  |
|     |          |     |      |                                   |          |      |     |      |  |
|     |          |     |      |                                   |          |      |     |      |  |
|     |          |     |      |                                   |          |      |     |      |  |
|     |          |     |      |                                   |          |      |     |      |  |
| 4   | 12-17-10 | BWG | MJVE | REVISED NOTE 1,MADE MAT'L. NYLON. | GB0239DA | 4    | PBC |      |  |
| REV | DATE     | BY  | CHK  | DESCRIPTION                       | ECN - R  | CUST | SUP | O.C. |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PMCC38H25-C](#) [PMCC38H25-M120](#) [PMCC38H25-M](#)