



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


1	VWS4218 (4) VWS4238 (4) ADCC31-AT-C10 (4) AMC25-AT-10 (2) VWS4274 (4) VWS42105 (4) HWS2B19 (4)	2	LWC25-A-14 (2) LWC25-H25-14 (1) LWC38-A-14 (2) LWC38-H25-14 (1) LWC50-A-14 (2) LWC50-H25-14 (1)	3	HCMP06B12-20 (2) HCMP06C12-20 (2) HCME06A12-130 (2)	4	BEC38-A (1) BEC75-A (1) BECP38H25 (1) BECP75H25 (1)	5	FCC-A-8 (2) FCC5-A-8 (2) FCM1-A-14 (1) LC10-A-L8 (1) LC3-A-8 (1) LC5-A-8 (1)	6	
7	TM156 (4) TM258 (4) TM3525 (4) TMEH-525-0 (2) TMTSHS13-0 (1)	8	ABMM-A (8) ABM1M-A (12) ABM25-A (8)	9	ABM100-A (8) ABM3H-A (2) ABM4H-A (2)	10	ABM112-A (8) SMS-A (1)	11	S1CH25 (4) S1CH38 (4) S1CH150 (2) WS25-25 (4) WS35-50 (4) WS50-50 (4) WS75-75 (4)	12	
13	CCS12-S8 (2) CCS25-S8-0 (2) CCS38-S8-0 (2) CCS50-S8-0 (2) CCH25-S10 (2) CCH50-S10 (2) CCH75-S10 (2) CCH100-S10 (1) CCH112-S10-0 (1) TWR (4)	14	ARC.68-A-14 (1) VCC25-A (4)	15	ACC19-A (2) ACC38-A (2) ACC62-A (2) PMCC38H25 (2)	16	AJC19-A (2) AJC25-A (2) AJC31-A (2) AJC38-A (2) A1C50-A-8 (2) A2C50-A-C8 (2)	17	PBMS-H25 (4) PM2H25 (4) PWMS-H25 (4) TM2PWH25 (4) MPMS19-0 (4) MPMS25-0 (4)	18	LPMM-S2 (4) LPMS-S8 (4) K1MS-H430-6 (4) K1MS-H366-2 (4) K1MS-H500-4 (4)
19	MCMS12-P (2) MCMS25-P (2) MCMS30-P (2) CPM122S (2) CPMB75 (2)	20	PLT-7M-M (6) PLT1.51-C (6) PLT1M-C (6) PLT25-C (6) PRT25-M6 (2) PLC1M-S4-C (2) PLF1M-M4Y (2) PLWP1M-C (2) ABM05-A-C (2)	21	LPFCM14-A-14 (2) LPFCM22-A-14 (2) GEE36F (6") GES2 (8") GES62 (6")	22	T25N (1) TS0F (1) TS0F-3Y (1) PP15-S12 (2) MP150 (2) MTP25-E10 (2) CLT25F 6 IN (1)	23	PLA25-A-0 (1) PRA25-A-0 (1) FCM-A-14 (1) FCH2-A-14 (1)	24	CBLS25 (4) CBLS50 (4) CBLS75 (4) CBP50 (4) CBP87 (4)



NOTE:

1. FORMAT IS AS FOLLOWS:
PRODUCT PART NUMBER (QUANTITY)

DIMENSIONS IN BRACKETS ARE METRIC [mm]

							TITLE				
							KP-509 KIT				
							CUSTOMER DRAWING				
							ITEM REVISION NAME				
							10B015KX/00				
							DATASET FILE NAME			MATERIAL: POLYPROPYLENE	
							10B015KX_DC/00-GB0239EG_REV09				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				
							.x ± 0.05 [1.3] .xxx ± 0.010 [0.25] .xx ± 0.02 [0.5] ANGLES ± 5 °				
--	---	--	--	--	SEE ECN FOR COMPLETE DETAILS.	---	 - THIRD ANGLE PROJECTION			DRAWING NUMBER: GB0239EG	
09	11/08/13	BWG	MPH	RTFI	UPDATED ARTWORK ON LID IN TOP VIEW. AND TITLE BORDER.	GB0239EG/09	DRAWN BY	DATE	CHK	SCALE	SIZE
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	JAD	6/2/00		NONE	A
							SHT 1 OF 1				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[KP-509](#)