


\* 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.



(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

# PANDUIT

BECP38H25  
BEVEL ENTRY CLIP

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

SCALE 2X

DRAWING NO.  
GB02391B

**DND**  
**A**  
**SIZE**

|     |         |     |     |   |          |     |      |     |  |  |
|-----|---------|-----|-----|---|----------|-----|------|-----|--|--|
|     |         |     |     |   |          |     |      |     |  |  |
|     |         |     |     |   |          |     |      |     |  |  |
|     |         |     |     |   |          |     |      |     |  |  |
|     |         |     |     |   |          |     |      |     |  |  |
|     |         |     |     |   |          |     |      |     |  |  |
|     |         |     |     |   |          |     |      |     |  |  |
| I   | 4/21/04 | JAD |     | PANEL THICKNESS WAS .09(2.3) MAX                        | 6802391B | I   |      |     |  |  |
| R   | 2/28/02 | LGG |     | INITIAL RELEASE TRANSFER FROM<br>DRAWING NUMBER G-01801 | 6802391B | R   |      |     |  |  |
| REV | DATE    | BY  | CHK | DESCRIPTION   | ECN      | - R | CUST | SUP |  |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[BECP38H25-L](#) [BECP38H25-L20](#) [BECP38H25-T](#) [BECP38H25-T20](#)