


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	COLOR	VALVE HANDLE SIZE in. (mm)	DIM. "A" in. (mm)	DIM "B" in. (mm)	DIM "C" in. (mm)	STANDARD PKG.
PSL-V9	RED	6.5-10.0 [165 to 254]	10.5 [266.7]	3.5 [88.9]	2.25 [57.15]	1
PSL-V13	RED	10.0-13.0 [254 to 330]	14.5 [368.3]	4.0 [101.6]	2.75 [69.85]	1
PSL-V2A	RED	1.0-2.5 [25 to 63.5]	3.5 [89.0]	.75 [19.05]	1.25 [31.8]	1
PSL-V6A	RED	2.5-6.5 [63.5 to 165]	7.0 [177.8]	2.0 [50.8]	1.75 [44.45]	1



SIMILAR TO C10094

NOTES:
1. MILLIMETERS
SHOWN IN ().
2. COLOR REQUIREMENT.

										PANDUIT	CORP	TINLEY PARK, ILLINOIS
										PSL - V*** GATE VALVE LOCKOUTS		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .032 (.XXX) ± .010 (.XX) ± .015 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
										DRAWN BY RVU	MAT'L:	SCALE NTS
O	3-29-06	RVU		ISSUE JAPAN CUSTOMER DWG.		4429	R			DATE 9-9-03	POLYPROPYLENE, RED PANTONE PMS 186	
REV	DATE	BY	CHK	DESCRIPTION		ECN	- R	CUST	SUP	CHK'D	C10401 DWG B SIZE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PSL-V2A](#) [PSL-V13](#) [PSL-V6A](#) [PSL-V9](#)