





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	PANEL DIMENSIONS		WEIGHT	
	THICKNESS	HOLE SIZE	lbs (g)	100 pcs
BEC3P75H25-___	0.118 MAX (3.0)	0.25 (6.4)	1.05 (475)	

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03415BA_DC_GB0239MG/01A

PANDUIT CORP. TINLEY PARK, ILLINOIS

BEVELED ENTRY CLIP WITH INTEGRAL PUSH BARB (BEC3P75H25)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE
PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE FULL

DATE 5/22/06

NYLON 6/6

DRAWING NO.
GB0239MG

DWG
A
SIZE

OIA	8-26-08	TMSA		REVISED GEOMETRY ADDED LOGO TO TOP	GB0239MG	OIA			
R	10-18-06	JAD		INITIAL RELEASE	GB0239MG	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[BEC3P75H25-T](#)