Network cable - NBC-M12MRA/0,3-937/M12MRA - 1409785

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

Assembled PROFINET cable, CAT5e, shielded, star quad, 22 AWG stranded (7-wire), black, angled M12 plug to angled M12 plug, line, length: 0.3 m

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	4 046356 881661
GTIN	4046356881661

Technical data

Dimensions

Length of cable	0.3 m

General data

Rated voltage	48 V AC
	60 V DC
Number of positions	4
Signal type/category	PROFINET

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab “Downloads”, Category “Manufacturer's declaration”

Phoenix Contact 2018 © - all rights reserved
http://www.phoenixcontact.com

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
http://www.phoenixcontact.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1409785