



Main

Range of product	9050JCK
Product or component type	Timer
Time delay type	One shot
Time delay range	0.6...60 s
[Uc] control circuit voltage	24 V AC/DC

Complementary

Hold-in power consumption in VA	2 VA
Line Rated Current	10 A
Switch function	DPDT
Contacts type and composition	2 NO + 2 NC
Contacts material	Silver nickel
Maximum switching voltage	240 V AC
Mounting support	Socket
Pin number	11
Shape of pin	Tubular
Product compatibility	8501NR61 8501NR62

Environment

product certifications	CE RoHS UL listed UL recognized
ambient air temperature for operation	-18...150 °F
height	2.4 in (61 mm)
width	1.69 in (43 mm)
depth	4.09 in (104 mm)

Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 0627 - Schneider Electric declaration of conformity	Compliant - since 0627 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Available	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9050JCK43V14](#)