



Main

Range of product	9050JCK
Product or component type	Timer
Time delay type	Repeat cycle
Time delay range	0.3...30 min
[Uc] control circuit voltage	24 V AC/DC

Complementary

Hold-in power consumption in VA	2 VA
Line Rated Current	10 A
Switch function	DPDT
Contacts type and composition	2 NO + 2 NC
Contacts material	Silver nickel
Maximum switching voltage	240 V AC
Mounting support	Socket
Pin number	8
Shape of pin	Tubular
Product compatibility	8501NR51 8501NR52

Environment

product certifications	CE RoHS UL listed UL recognized
ambient air temperature for operation	-18...150 °F
height	2.4 in (61 mm)
width	1.69 in (43 mm)
depth	4.09 in (104 mm)

Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 0627 - Schneider Electric declaration of conformity	Compliant - since 0627 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Available	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9050JCK57V14](#)