









SCHEMATIC




QG3F





Ø0.74
[18.9]



366
FEMALE XLR TO BNC



QG3M



Ø0.74
[18.9]



367
MALE XLR TO BNC

CUSTOMER DRAWING

NOTES:

1. MATERIALS:
ADAPTER HOUSING - ZINC, NICKEL PLATED
BNC HOUSING -COPPER ALLOY, NICKEL PLATED
BNC CONTACT - COPPER ALLOY, GOLD PLATED
QG3M OR QG3F XLR CONNECTOR
2. THESE PRODUCTS ARE RoHS COMPLIANT.

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.02 - THREE PLACE DECIMALS ±0.005	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
						SIZE	WIDTH		MULT		LBS/M		TEMPER		
						FINISH						MATERIAL			
						SPEC No.						SPEC No.			
C	26634	10-08-10	JEB	TJK		FIRST USED ON				SCALE 1.5:1		Switchcraft®			
B	26594	08-12-10	JEB	TJK		DATE DRAWN 1/2/08	BY BS	CHKD JEB 08-14-09		APVD TJK 01-10-11					
A	26407	6-25-09	JEB	TJK								SHEET 1 OF 1			
REV	ECO NUMBER	DATE	BY	APVD	NAME XLR TO BNC IMPEDANCE MATCHING ADAPTER, RoHS						PART No. 366-367			REV C	
REVISIONS					DO NOT SCALE DRAWING										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[367](#)