

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		FIRST ISSUE	14MAY07	DC	TdB
A1		REVISED PER ECO-09-026495	NOV09	KK	AEG

NOTES:

- 1) CABLE DIAMETER 3 TO 11 MM DEPENDING ON PLACEMENT OF THE GROMMET.
2) MINIMUM ORDER QUANTITY FOR ALL PARTNUMBERS 100 KITS

3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



D-SUBMINIATURE COVER KIT			
PARTNUMBER	POSITION	THREAD JACKSCREW	COLOR
5-885000-1	9	#4-40 UNC	BLACK
5-885000-2	15	#4-40 UNC	BLACK
5-885000-3	25	#4-40 UNC	BLACK
5-885000-4	39	#4-40 UNC	BLACK
2-885000-1 3	9	M3	BLACK
2-885000-2 3	15	M3	BLACK
2-885000-3 3	25	M3	BLACK
2-885000-4 3	39	M3	BLACK

ITEM	QTY	DESCRIPTION	MATERIAL
1	1	COVER	NYLON 6 UL94V-2
2	2	JACKSCREW	NI PLATED BRASS
3	1	GROMMET	NYLON 6 UL94V-2
4	1	CABLE CLAMP	ZN PLATED STEEL
5	2	SELF TAPPING SCREW	ZN PLATED STEEL

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±

MATERIAL	FINISH
-	-

DWN	14MAY07
CHK	D.CAMPSCHROER
D.CAMPSCHROER	14MAY07
APVD	14MAY07
T. DE BOER	
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	-

tyco <i>Electronics</i>		TYCO ELECTRONICS NEDERLAND B.V. 's-HERTOGENBOSCH, THE NETHERLANDS	
NAME			
SUB-D COVER KIT; 9, 15, 25 OR 39 POS. M3 OR #4-40 UNC TRHEADED JACKSCREW			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C- 2-885000-1	-
		SCALE NTS	SHEET OF REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-885000-3](#)