



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AH	REVISED PER ECO-12-012316	05JUL12	KH	MZ
	AJ	REVISED PER ECO-16-017885	06OCT2017	RS	MZ



$1.90^{+0.13}_{-0.25}$
 $1.52^{+0.25}_{-0.13}$
 $0.075^{+0.005}_{-0.010}$
 $0.060^{+0.010}_{-0.005}$
 TYP

13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

- | | | | | | | |
|----|----------|----------|--------------------|----|--------------------|-----------|
| 13 | OBSOLETE | 1 | 12 | 11 | — | 1—66106—7 |
| | OBSOLETE | STANDARD | | | 1—66107—1 | 1—66106—6 |
| | | 1 | 11 | | 1—66107—1 | 1—66106—5 |
| | OBSOLETE | 1 | | 10 | 66107—8 | 1—66106—4 |
| | OBSOLETE | 1 | 5 | | 66107—7 | 1—66106—2 |
| | | 1 | 2 | | 66107—4 | 66106—8 |
| | | 1 | 4 | | 66107—3 | 66106—7 |
| | OBSOLETE | 1 | 7 | | 66107—2 | 66106—6 |
| | | 1 | 3 | | 66107—1 | 66106—5 |
| | STANDARD | | 2 | | 66107—4 | 66106—4 |
| | | STANDARD | 4 | | 66107—3 | 66106—3 |
| | | STANDARD | 7 | | 66107—2 | 66106—2 |
| | OBSOLETE | STANDARD | 3 | | 66107—1 | 66106—1 |
| | | REELING | P/N BODY
FINISH | | LOOSE PIECE
REF | PART NO |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 7-17-91 R. SHIREY CHK 8-15-91 R. STONE APVD 8-19-91 J. WESTMAN		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN ASSEMBLY, .062, TYPE III+	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -			
MATERIAL SEE CALLOUTS		FINISH SEE TABLE			
		WEIGHT -		SIZE A2 CAGE CODE 00779 DRAWING NO. C=66106	
		CUSTOMER DRAWING		SCALE 8:1 SHEET 1 of 1 REV AJ	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66106-5](#)